

Operating System	Windows 11 Home
Chassis/ Color	Black
Chipset	Intel® B560
Processor	Core i7-12700F
CPU Speed	2.1GHz up to 4.9GHz
CPU Cooler	Fan Cooler
Graphic	RTX 3070 8GB GDDR6
Graphic Memory	8GB GDDR6
System Memory	U-DIMM DDR4 16GB 3200 (8G*2)
Memory Total Slots	2x DDR4 3200MHz SO-DIMMs, up to 64GB
SSD / Hard Drive	1TB M.2 PCIE SSD
Storage Slots (Total/Free)	2x M.2 2280 SSD (Front 1x PCIe Gen 4, Rear 1x SATA/PCIe Gen 4 combo) 2x 2.5" Drive bays
LAN	Realtek RTL8125B ethernet
Wireless LAN	Intel Wi-Fi 6E AX211
Bluetooth	BT 5.2
Audio	7.1 Channel HD Audio with Nahimic 3 audio boost
Mic-in/Headphone-out	1/1
USB	Front: 1x USB 3.2 Gen 1 Type A, 1x USB 3.2 Gen 1 Type C Rear: 3 x USB 3.2 Gen 2 Type A, 1 x USB 3.2 Gen 2 Type C
USB 2.0	Front: 1x USB 2.0 Type A Rear: 2 x USB 2.0 Type A
Other port	Rear: 1x HDMI 2.0b with HDR port, 1x DisplayPort 1.4 port, 3 x Audio jacks, 1 x RJ45(2.5Gb LAN)
KB/Mouse	GK 30 + GM11
Power Supply	750W 80 Plus Gold certified (SFX)
Dimension	137.06 x 396.57 x 410.39 mm / 5.4 x 15.61 x 16.16 inches
Chassis (liters)	10.36L / 21.89pt
Weight (LB)	7.9 Kg / 15.63 lbs
UPC	824142276839
UCC-14	10824142276836
Warranty	1 Year Warranty