



Raider GE66 12UGS-025CA

OS	Windows 11 Home
Color	Titanium Blue
Screen Size / Type	15.6" FHD (1920*1080), 360Hz, close to 100%sRGB
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-12700H 6+8Core
CPU Frequency	1.7-4.7GHz
Graphics	NVIDIA GeForce® RTX3070TI Laptop GPU
Video Memory	8G GDDR6
System Memroy	DDR5 8GB*2 4800MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	512GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2x M.2 SSD Slot PCIe Gen4x4
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
BT	BT 5.2
Card Reader	SD7.0
HDMI-out	v2.1,
Mini-Display Port	v1.4
USB Type C	1x Thunderbolt 4 1x USB 3.2 Gen 2/DP
USB	1 x Type-A USB3.2 Gen2, 2 x Type-A USB3.2 Gen1
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Sound by Dynaudio, 2x2W Speaker
Webcam	1080p FHD Webcam
Battery Pack	4 cell (99.9Whr) Li-Ion
AC Adapter	280W
Unit weight	5.25 lbs
Unit Dimension	14.09"x 10.51"x 0.92"
UPC	824142275054
UCC-14	10824142275051
Warranty	1 year Limited warranty (Include 1 Year Global)