

OS	Windows 11 Home
Color	Core Black
Screen Size / Type	17.3" FHD (1920x1080), 360Hz 3ms, IPS-Level
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-12700H 6+8Core
CPU Frequency	1.7-4.7GHz
Graphics	NVIDIA GeForce® RTX3070TI Laptop GPU
Video Memory	8G GDDR6
System Memroy	DDR IV 8GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2x M.2 SSD Slot PCIe Gen4x4
LAN	2.5GbE
WLAN	Killer WiFi 6E AX211 (2x2)
BT	BT 5.2
HDMI-out	v2.1,
Mini-Display Port	v1.4
USB Type C	1x USB 3.2 Gen2/DP
USB	3x USB3.2 Gen 1
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (102 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Speakers 2W*2
Webcam	720p HD Webcam
Battery Pack	4 cell (65Whr) Li-Polymer
AC Adapter	280W
Unit weight	6.39 lbs
Unit Dimension	15.63"x 11.18"x 1.02"
UPC	824142276624
UCC-14	10824142276621
Warranty	1 year Limited warranty (Include 1 Year Global)