



BUSINESS DEVICES THAT ARE A CLASS APART



The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

ThinkPad T14 Gen 2 (Intel)

Smarter
technology
for all

Lenovo

MIL-SPEC tested durability, a battery that can last up to 16 hours and a suite of reliable security features make this 14" business laptop the ideal companion device for the road. Although thin and light, it does not compromise on performance. It features the latest 10th Gen Intel Core processors, ultra-fast SSD storage, and modern connectivity ports such as USB-C and ThunderBolt 3 for responsive performance and seamless multitasking.



REASONS TO BUY

Experience uninterrupted productivity with features like Modern Standby that allows the device to receive important updates even with the lid closed and resume from standby in an instant. Optional 4G WWAN module enables reliable connectivity when WiFi signal is weak or unavailable

Prioritizes privacy and security. Optional PrivacyGuard technology renders the display unreadable for shoulder surfers. Other security features include optional IR camera with built-in privacy shutter, onboard fingerprint reader and data encryption technologies.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

ThinkPad T14 Gen 2 (Intel)

KEY SPECIFICATIONS

Processor	Up to 11th Gen Intel Core i7 processor
Operating System	Powered by Windows 10 Pro
Display	14.0" Dolby Vision HDR 400 screen, 4K (3840x2160) IPS, 1500:1 contrast ratio, 100% Adobe RGB, 500 nits 14.0" PrivacyGuard screen, FHD (1920x1080) IPS, 1000:1 contrast ratio, 72% NTSC, 500 nits (touch) 14.0" Low Power screen, FHD (1920x1080) IPS, 800:1 contrast ratio, 72% NTSC, 400 nits 14.0" screen, FHD (1920x1080) IPS, 700:1 contrast ratio, 45% NTSC, 300 nits (touch) 14.0" screen, FHD (1920x1080) IPS, 700:1 contrast ratio, 45% NTSC, 300 nits
Touchscreen	Optional touchscreen on regular Full HD model
Graphics	Intel UHD or Iris Xe Graphics in processor, optional NVIDIA GeForce MX450 2GB
Memory	Up to 48GB DDR4-3200
Storage	One drive, 1x M.2 2280 SSD (up to 2TB) or 1x M.2 2242 SSD (up to 128GB)
Audio	2x2W speakers with Dolby Audio speaker system Dual array far-field mics
Battery†	Up to 10.7hrs (50Whr)
Power Adapter	One of the following 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)
Camera	One of the following 720p with Privacy Shutter IR & 720p with Privacy Shutter
Keyboard	Spill resistant, optional backlit, Unified Communication keys
Dimensions	From Width: 329mm (12.95") Depth: 227mm (8.94") Height: 17.9mm (0.70")
Weight	Starting at 1.47kg (3.23lb)

GREEN CERTIFICATIONS

EPEAT Gold, Energy Star 8.0

OTHER CERTIFICATIONS

MIL-STD-810H military testing

CONNECTIVITY

I/O Ports	1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 2x Thunderbolt 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a), 1x HDMI® 2.0, 1x microSD card reader, optional 1x Ethernet (RJ-45), 1x headphone / microphone combo jack (3.5mm), 1x side docking connector, optional 1x Smart card reader, optional 1x RFID reader, and 1x Nano-SIM card slot (WWAN models)
RFID Reader	RFID Reader
WLAN + Bluetooth	One of the following Intel AX201 11ax, 2x2 + BT5.2 Intel AX210 11ax, 2x2 + BT5.2
WWAN	Optional
NFC	Optional
Docking	Compatible with Side Mechanical dock and USB 3.0 & USB-C docking solutions

SECURITY & PRIVACY

Fingerprint Reader
Smart Card Reader
IR Camera with Windows Hello
ThinkPad PrivacyAlert
ThinkPad PrivacyGuard screen
Match on Chip Touch Fingerprint Reader (optional)
RFID and FIPS Fingerprint Reader (optional)
TPM 2.0 chip
Web camera privacy shutter
ThinkPad PrivacyGuard with On-Cell Touch (optional)
Kensington™ Security Slot

MANAGEABILITY

Intel vPro, DASH (optional)

Recommended for this device



Lenovo Powered USB-C Travel Hub

Connects to a PC through a single USB-C cable which also recharges the device

Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports

Compact 183x100mm (7.2x4") design with integrated cable management



Lenovo 700 Ultraportable Bluetooth Speaker

Just 11mm (0.43") thin and weighing 145g (0.32lb), this ultra-thin Bluetooth speaker delivers 360-degree sound with 2x 2Watt power output

Supports Siri and Google Assistant voice commands for your iOS and Android devices, as well as a dedicated button for taking calls

Fast-charges in 2 hours and lasts for up to 12hours of audio playback or voice calls



Premier Support

Talk directly with advanced technical support agents

Support for software & hardware

Next business day onsite repairs

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.