



Maximizing enjoyment of the latest HDR entertainment content, EW2880U leverages 4K UHD IPS panel with HDRi and superior audiovisual features to deliver immersive multimedia experience. Featuring BenQ proprietary HDRi technology, FreeSync plus remote control and USB Type-C, EW2880U is to take your video enjoyment to the next level.



# **BenQ Entertainment Monitor EW2880U**



# See with Eyes Widened

HDRi:

#### Cinema HDRi

refines color, brightness, and clarity for stellar visual performance



#### Game HDRi

subtle color and brightness gradations reveal invisible details



### 90% DCI-P3

makes colors more vivid, delivering cinematic-quality entertainment



#### Racing mode

race towards your goal with a wider field of view and clear images









## Let the Sound Strike a Chord



#### Night mode

gives lowered voices more clarity for quiet viewing at night



(( ) 3W Stereo conveys resounding stereo sound with clear details



Integrated sound systems bring truly expansive sound to your movies, binge-watching and gaming. Take your audiovisual enjoyment to the next level with instant audio excellence without cable messes.



















Rock / Party

# Plug in and Start My Day

It's simple. Set ergonomic height and tilt settings to your ideal levels. Connect all your peripherals through varied ports, including the latest single-cable USB-C™ with power delivery.Then, select your content and settle in for a great time!













Dimension & Weight		
Dimensions (H x W x D mm) (w/o Base)	373 × 637 × 71	
Dimensions (H × W × D mm)	521 × 637 × 277	
Net Weight (kg)	7.9	
Gross Weight (kg)	10.7	
Special Features		

	opeciai i cacai es	
HDCP	٧	
Display Mode	Full/Aspect Ratio/I:I	
B.I.+	٧	
Eye reminder	٧	
Color weakness	V	
e-Paper Mode	V	
Low blue light	٧	
Flicker Free	٧	
IR remote controllor	٧	
HDR Mode	V	
OSD Language	18 languages	
1.1.1.14		

Included Accessories		
Other Accessories	Power cord(1.5m)/HDMI 2.0 cable(1.8m) /USB-C(1.0m)/Remote Control/QSG	
VO		
HDMI Input (2.0)	2	
Display Port (1.4)(DP1.2+HDR)	1	
USB-C (PD 60W, w/ DP Alt mode)	1	
Headphone jack	v	
Power		
Power Supply (90~264 AC)	Built in	
Power Consumption (On mode)	35W	
Power Consumption (Power saving mode)	< 0.5W	

Tower Supply (** =*****)	- 0.5**
Certification	
TUV Certificate	TUV Flicker-free, TUV Low Blue Light
Windows® Compatible	Windows® 10, 8.1, 8, 7

© 2021 BenQ Corp. Specification may vary by region, please visit your local stores for details. Actual products features and specifications are subject to change without notice. This material may include corporate names and trademarks of third parties which are the properties of the third parties respectively. Doc: LCD\_EV/2880U\_DS\_EN\_190819





r Supply (90~264 AC)