

OS	Windows 11 Home
Color	Black
Screen Size / Type	17.3" FHD (1920*1080), 360Hz, close to 100% sRGB
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-12700H 6+8Core
CPU Frequency	1.7-4.7GHz
Graphics	NVIDIA GeForce® RTX3070 Laptop GPU
Video Memory	8G GDDR6
System Memory	DDR IV 8GB*2
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	Up to 2 x NVMe PCIe Gen4 SSD
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
BT	BT 5.2
HDMI-out	4K @ 60Hz
USB Type C	1x USB 3.2 Gen1
USB	2x USB 3.2 Gen1 1x USB 2.0
Keyboard	Single zone RGB keyboard with Anti-Ghost key (99 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	2W*2
Webcam	720p HD Webcam
Battery Pack	3 cell (53Whr) Li-Polymer
AC Adapter	240W
Unit weight	6.17 lbs
Unit Dimension	15.68"x 10.76"x 0.95"
UPC	824142279694
UCC-14	10824142279691
Warranty	1 year Limited warranty (Include 1 Year Global)