

OS	Windows 11 Pro
Color	Core Black
Screen Size / Type	15.6" FHD, Anti-Glare Wide View Angle 240Hz 3.5ms
Resolution/ Ratio	1920x1080 16:9
CPU/Processor	Core i7-12700H 6+8Core
CPU Frequency	1.7-4.7GHz
Graphics	NVIDIA GeForce® RTX3060 Laptop GPU
Video Memory	6G GDDR6
System Memroy	DDR5 8GB*2 4800MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	512GB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2x M.2 SSD Slot PCIe Gen4x4, (Max up to 2TB)
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2 )
BT	BT 5.2
HDMI-out	v2.1,
USB Type C	1x Thunderbolt 4 2x USB 3.2Gen2/DP
USB	2x USB3.2 Gen2
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Touch Pad	Silky Glass Touchpad
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Dynaudio Speakers 2W*2
Webcam	IR HD
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	240W
Unit weight	4.63 lbs
Unit Dimension	14.11"x9.76"x0.78"
UPC	824142280645
UCC-14	10824142280642
Warranty	1 year Limited warranty (Include 1 Year Global)