

OS	Windows 11 Pro
Color	Core Black
Screen Size / Type	17.3" QHD, Anti-Glare Wide View Angle 240Hz 3ms DCI-P3 100%
Resolution/ Ratio	2560x1440 16:9
CPU/Processor	Core i7-12700H 6+8Core
CPU Frequency	1.7-4.7GHz
Graphics	NVIDIA GeForce® RTX3070TI Laptop GPU
Video Memory	8G GDDR6
System Memroy	DDR5 16GB*2 4800MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2x M.2 SSD Slot PCIe Gen4x4
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
BT	BT 5.2
Card Reader	SD7.0
HDMI-out	v2.1,
USB Type C	1x Thunderbolt 4 1x USB 3.2Gen2/DP
USB	2x USB3.2 Gen2
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (99 Key)
Touch Pad	Silky Glass Touchpad
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Sound by Dynaudio, 4x 2W Woofers + 2x Speaker
Webcam	IR FHD
Battery Pack	4 cell (99.9Whr) Li-Polymer
AC Adapter	240W
Unit weight	6.17 lbs
Unit Dimension	15.65"x 11.16"x 0.79"
UPC	824142280676
UCC-14	10824142280673
Warranty	1 year Limited warranty (Include 1 Year Global)