

Manufacturer Part #	RaiderGE6612235
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU	Core i9-12900HK
CPU Speed	1.8-5 GHz
Chipset	-
Color	Titanium Blue
Screen Size	15.6" UHD, Anti-Glare Wide View Angle 4K 120Hz Thin Bezel, Adobe 100%
Resolution	3840x2160 (16:9)
GPU	NVIDIA® GeForce RTX™ 3080 TI Laptop GPU Up to 1555MHz Boost Clock, 150W Maximum Graphics Power with Dynamic Boost. Max. 195W CPU-GPU Power with MSI OverBoost Technology. *May vary by scenario
Video Memory	16G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Audio	Nahimic 3 / Hi-Res Audio
Speaker	Sound by Dynaudio, 2x2W Speaker
Memory	32GB (16G*2) DDR5 4800MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	1080p FHD Webcam
USB	1x USB3.2 Gen 2; 2x USB3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	1x (8K @ 60Hz / 4K @ 120Hz) HDMI ; 1x Mini-DisplayPort
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	280W
Battery Pack	4 cell (99.9Whr)
Dimension	14.09"x 10.51"x 0.92"
Weight	5.25 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)