

| | |
|-----------------------|--|
| Manufacturer Part # | CreatorZ16046 |
| OS | Windows 10 Pro (MSI recommends Windows 11 Pro for business.) |
| CPU | Core i7-11800H 8 Core |
| CPU Speed | 2.4 - 4.6GHz |
| Chipset | HM570 |
| Color | Lunar Gray |
| Screen Size | 16" QHD+ (2560*1600), 120Hz DCI-P3 100% typical, Finger Touch panel |
| Resolution | 2560x1600 (16:10) |
| GPU | NVIDIA® GeForce RTX™ 3060 Laptop GPU Up to 1357MHz Boost Clock, 65W Maximum Graphics Power with Dynamic Boost. *May vary by scenario |
| Video Memory | 6G GDDR6 |
| Keyboard | miniLED Per key RGB backlight KB (84 Key) |
| Audio | Nahimic 3 / Hi-Res Audio |
| Speaker | Dynaudio Speakers 2W*4 |
| Memory | 16GB (8G*2) DDR4 3200MHz |
| HDD Capacity | 512GB NVMe SSD |
| HDD Interface | NVMe |
| Optical Drive Type | - |
| LAN | - |
| WLAN | Killer WiFi 6E AX1675 (2x2) |
| Bluetooth | BT 5.2 |
| Card Reader | Micro SD |
| Webcam | IR 720p HD Webcam |
| USB | 2x USB 3.2 Gen2 |
| Type-C Port | 2x Thunderbolt™ 4 |
| Video Port | - |
| Audio Port | Mic-in/Headphone-out Combo |
| AC Power Adaptor | 180W Slim |
| Battery Pack | 4 cell (90Whr) |
| Dimension | 14.13"x10.08"x0.64" |
| Weight | 5.07 lbs |
| Manufacturer Warranty | 1 year Limited warranty (Include 1 Year Global) |