



**Work. School. Fun. It all looks good from here.**

Welcome home to your window to the world. Top-quality picture with a 5MP camera, amazing sound and sleek design makes this elegant 23.8" monitor become the centerpiece of your connected daily life. It's designed for ease and simplicity without compromising quality so you can feel as good as you look. Hop from a call to a class to whatever else in stride and see the complete picture of it all.



#### **Look & Sound Better Than Ever**

Behold the new 23.8" conferencing monitor with an integrated 5 megapixel camera and behold...yourself. That's nearly twice the resolution of a standard webcam. Just hop on your call and hold on tight, the compliments will be coming in hot. Enjoy rich audio and noise-cancelling dual microphones so you can sound as good as you look. There's also a physical sliding camera cover so you can ensure your camera is off when you need it to be.

#### **Make Yourself Look & Sound Like Yourself**

Make yourself look as good as you should. HP Display Center gives you control of how you look and sound. Adjust camera settings and use the preview window to dial in your picture to perfection.

#### **Clear Desk. Clear Mind.**

Connect with success and disconnect from the mess with a simple, Works With Chromebook certified setup. Because it's WWCB certified, your monitor simply works<sup>[1]</sup> with your Chromebook and other Chrome OS devices<sup>[2]</sup>. A seamless integrated conferencing set up using one USB-C<sup>®</sup><sup>[3]</sup> cable. Easily connect your peripherals to the monitor's port hub, sleekly tucked in behind. Now that's the picture of simplicity.

#### **Featuring**

##### **Looks Good. Does Good.**

Both the display and stand are made with 85% PCR with 5% OBP and the packaging is sustainably sourced and recyclable. <sup>[5,6]</sup>

##### **Integrated speakers**

Get great audio built right in from the integrated speakers.

##### **HP Webcam**

Clear, smooth video chats so you can stay in touch with the whole family. <sup>[7]</sup>

##### **Adjust your view**

Adjust your screen's height for comfortable viewing with swivel and tilt capability.

##### **Easily personalize and adjust your display.**

Customize your display with easy, intuitive HP Display Center software that lets you tailor your settings, partition screens, and even dim the screen.

## Specifications

<b>Display size (diagonal)</b>	23.8"
<b>Panel technology</b>	IPS
<b>Display size (diagonal)</b>	60.45 cm (23.8")
<b>Aspect ratio</b>	16:9
<b>Native resolution</b>	FHD (1920 x 1080) <sup>[1,5]</sup>
<b>Resolutions supported</b>	640 x 480; 720 x 400; 800 x 600; 1024 x 768; 1280 x 720; 1280 x 800; 1280 x 1024; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080
<b>Pixel pitch</b>	0.2745 mm x 0.2745 mm
<b>Brightness</b>	300 nits <sup>[1]</sup>
<b>Contrast ratio</b>	1000:1
<b>Response time (typical)</b>	5ms GtG (with overdrive) <sup>[1]</sup>
<b>Minimum dimensions (W x D x H)</b>	53.95 x 4.79 x 37.22 cm (Without stand.)
<b>Minimum dimensions (W x D x H)</b>	21.24 x 1.89 x 14.65 in (Without stand.)
<b>Dimensions With Stand (W x D x H)</b>	53.95 x 21.14 x 52.34 cm
<b>Weight</b>	6.3 kg (With stand.)
<b>Weight</b>	13.86 lb (With stand.)
<b>Display features</b>	On-screen controls; AMD FreeSync™; Low blue light mode; Dual speakers (2W per channel); Anti-glare; Height adjustable; Webcam; Integrated microphone; Works With Chromebook Certified
<b>Onscreen controls</b>	Brightness; Exit; Information; Management; Power control; Input control; Menu control; Image; Color
<b>Display scan frequency (horizontal)</b>	30-85 KHz
<b>Display scan frequency (vertical)</b>	48-75 Hz
<b>Camera</b>	Yes, 5MP
<b>Power</b>	100 - 240 VAC 50/60 Hz
<b>Power consumption</b>	120 W (maximum), 20 W (typical), 0.5 W (standby)
<b>Operating temperature range</b>	5 to 35°C
<b>Operating humidity range</b>	20 to 80% non-condensing
<b>Sustainable impact specifications</b>	85% post-consumer recycled plastic; Low Halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Contains Ocean-Bound plastic
<b>Certifications and compliances</b>	Argentina S-Mark; BIS; CB; CCC; CE; CEL; CEL Grade 1; C-Tick; cTUVus; ENERGY STAR®, EPA; EUP Lot-5; EUP Lot-6; FCC; GS Mark; ICES; ISO 9241-307; KC/KCC; NOM; NOM (Mexico); RCM; UL/CSA-NRTL/ETL-NRTL Mark; VCCI; WEEE; EUP Lot-26; California Energy Commission (CEC); South Africa Energy; eStandby; Mexico LASE form; ICE; KES; PSE EAC; India BIS
<b>Physical security</b>	Security lock-ready <sup>[2]</sup>
<b>Management Software</b>	HP Display Center
<b>UPC number</b>	(A2K) 195908994220; (AB0) 195908994237; (AB1) 195908994244; (AB2) 195908994251; (AB4) 195908994268; (ABG) 195908994275; (ABJ) 4573595660301; (ACJ) 195908994282; (AKL) 195908994299; (AR6) 195908994305; (UUF) 195908994312
<b>What's in the box</b>	Monitor; HDMI cable; Warranty card; QSP; 1 USB Type-C® to Type-C cable; 1 USB Type-C® to Type-A cable; AC power cord

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

- [1] Gmail account required for full functionality.
- [2] Google tested to meet Chromebook compatibility standards. This product works with devices capable of running the latest version of Chrome OS and has been certified to meet Google's compatibility standards. Google is not responsible for the operation of this product or its compliance with safety requirements. Chromebook and the Works With Chromebook badge are trademarks of Google LLC.
- [3] USB Type-C® and USB-C® are trademarks of USB Implementers Forum.
- [5] Based on HP's internal analysis. Monitor's 85% post-consumer recycled plastic content consists of 5% ocean bound plastic materials by weight.
- [6] 100% outer box/corrugate cushion packaging made from sustainably sourced certified and recycled fibers. Fiber cushions made from 100% recycled wood fiber and organic material. Excludes plastic bags and plastic foam sheeting.
- [7] Features may require software or other 3rd party applications to provide the described functionality.

## Technical Specifications Footnotes

- [1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.
- [2] Lock sold separately.
- [5] DisplayPort™ 1.2 or HDMI 1.4 or USB Type C® (Alt Mode DisplayPort™ compatible) required to drive panel at its native resolution. The video card of the connected PC must be capable of supporting 1920 x 1080 at 60 Hz with 8-bit color using one DisplayPort™, HDMI, or USB Type C® (Alt Mode DisplayPort™).

---

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. EyeSafe® is a registered trademark of EyeSafe, Inc.

