IP

4 Channel Surveillance Kit with Four 5MP IP Cameras, 1TB, NDAA Compliant

IR | IP66 | H.265 | EZ WIZARDS | PoE | S.M.A.R.T.

ZIPK4N1

4-Channel Network Video Recorder with 4 Built-In PoE Ports

4 5MP IP Cameras

Front panel

Rear panel

5 YEAR WARRANTY

Key Features

EZ Wizard: Simple network and system setup

EZ Record: Setup recording resolutions and recording type

EZ Copy: Copy what you are playing onto a USB flash drive

EZ App Setup: Just scan a QR code with the app to view your cameras on your mobile device

Recorder Features

• Up to 8MP resolution for live view, recording, and playback
• Plug & Play – get video automatically via the PoE ports without any setup
• Supports streams up to H.265 for reduced bandwidth and reduced hard drive space requirements
• QR code based network setup for easy remote access
• Free US-based DDNS service
• 4K monitor output
• Gigabit Ethernet port
• Built-in S.M.A.R.T technology (Self-Monitoring, Analysis and Reporting Technology for HDD)
• Remote monitoring via PC, Mac, and mobile apps
• 1TB storage
• Analytics available with optional **O8K1A** camera
    • Facial Recognition
    • Human Detection
    • Vehicle Detection

Camera Features:
(Only works with this kit)

• Supports up to 5MP resolution
• 2.8mm wide angle lens
• True Day/Night operation (IR cut filter)
• IR range up to 100ft (built-in IR LEDs)
• Supports H.265/H.264 compression
• IP66 compliant, weather resistant

What's in the box:

• NVR with 1TB hard drive
• Four 5MP cameras
• Four 60ft Ethernet cables
• One 3ft Ethernet cable
• Remote control (batteries included)
• USB optical mouse
• 48V Power adapter
• HDMI cable

ZIPK4N1

Camera Specifications

Image Sensor	1/2.7" 5MP CMOS
Resolution	2592 x 1944
Minimum Illumination	BW: 0 lux (IR LED on), Color: 0.05 lux @ F1.2 (AGC on)
Day/Night	IR cut filter with auto
Compensation	DWDR
White Balance	Auto / Manual / Indoor
Electronic Shutter Speed	1/5 ~ 1/20000 sec
DNR	3D
IR Range	100ft. (depending on scene reflection)
Compression	H.265, H.264
Bitrate Control	VBR, CBR
Multiple Streaming	2 streams
Ethernet	10/100 Mbps
Power	12VDC (power supply not included)
Power Consumption	7W
Operating Temperature	-22°F - 131°F
Operating Humidity	0% - 90% RH
Unit Dimensions	3.35" (H) x 3.55" (Dia.)
Unit Weight	1.5 lbs.
Camera Model Number	O5K1

Recorder Specifications

Max. Bit Rate	128 Mbps
Max. Recording Resolution	8MP
PoE Ports	4
Monitor Output	1 HDMI, 1 VGA
Display Resolutions	VGA: 1024 x 768, 1280 x 720, 1280 x 1024, 1440 x 900, 1920 x 1080 HDMI: 1024 x 768, 1280 x 720, 1280 x 1024, 1440 x 900, 1920 x 1080, 2560 x 1440, 3840 x 2160/EDID
USB Ports	1 x USB 2.0 (Front), 1 x USB 2.0 (Rear)
HDD Slots	1 (Up to 1TB)
Ethernet	RJ-45 (100/1000M) port
Remote Viewing	Speco Gray Viewer (Windows, Mac), Speco Gray app (iOS, Android), Apple TV and Amazon Fire TV
Power Supply	48VDC, 1.5A (included)
Dimensions	11.8" (W) x 2.1" (H) x 8.9" (D)
Model	N4JLN

Optional Accessory

O8K1A
Analytic Camera

O5KJBD
Camera Junction Box

O5KWMT
Wall Mount

Speco GRAY

NDAA COMPLIANT

*Products are in compliance with NDAA Section 889 Part B Guidelines

RESI-CAM®