




HP OfficeJet Pro 8025e All-in-One Printer w/ 6 months free ink through HP Plus

Essential, all-around productivity

This printer is best for shared home offices doing a range of print tasks, including professional color documents and even a few photos. Count on the fast print speeds up to 20 ppm⁷, automatic two-sided printing, and reliable Wi-Fi connectivity.²



This is an HP+ enabled printer. Choose HP+ at product setup to activate benefits. HP+ requires an HP account, connection to the internet, and exclusive use of Original HP Ink cartridges for the life of the printer. More at: <http://www.hp.com/plus-faq>. This printer uses dynamic security, which may be updated periodically by firmware updates. The printer is intended to be used solely with cartridges using an original HP chip. Cartridges using a non-HP chip may not function or may cease to function. More at: <http://www.hp.com/learn/ds>

ISO Speed: Black: Up to 20 ppm; Color: Up to 10 ppm
Print Resolution: Black (best): 1200 x 1200 rendered dpi; Color (best): Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Scan Resolution: Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi
Copy Resolution: Black (text & graphics): Up to 600 dpi; Color (text & graphics): Up to 600 dpi
Fax Resolution: Black (best): Up to 300 x 300 dpi; Color (best): 200 x 200 dpi
Standard Connectivity: 1 USB 2.0; 1 Ethernet; 1 Wireless 802.11a/b/g/n; 1 RJ-11 Fax
Mobile Printing Capability: Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified; HP Smart
Duty cycle: Monthly (letter): Up to 20,000 pages
Display: 2.7" (6.86 cm) Capacitive Touchscreen CGD (Color Graphic Display)

Designed to save you time

- Eliminate steps in repetitive tasks, using Shortcuts.¹ Scan to the cloud, email, and more – in a tap.¹
- Work fast and hands-free with the 35-page auto-feeder. Get automatic two-sided printing.
- Take control of print, scan, copy, and fax jobs with tap-and-swipe ease, using the color touchscreen.

Freedom to work anywhere

- Connect to cloud-based printing with Wi-Fi™ or your cellular network to print from anywhere.¹
- Quickly access and print documents and images on your smartphone, from Dropbox and Google Drive.¹
- Get high-quality scanning to share to Dropbox, Google Drive, email, or the cloud – from virtually anywhere.¹
- Get notifications when printing, scanning, or copying from your smartphone.¹

HP+: Printing made brilliantly simple

- Get 6 months of free ink with HP Instant Ink⁶ and 2 year extended HP warranty when you activate HP+ when you set up your printer
- 6 months of free ink with Instant Ink⁶: Enough to print up to 700 pages a month and HP will automatically send new ink when you run low. Credit card needed to enroll. Cancel or change any time.
- After 6 months you can continue with HP Instant ink to get ink delivered automatically when you need it for up to 50% less³

Enhanced security, reliable connections

- Reduce interruptions with self-healing Wi-Fi™ that keeps you connected.²
- Get security essentials to help maintain privacy and control.
- Count on chatbot support and helpful notifications with the HP Smart app.¹
- Easily share resources – access and print with wireless networking.²



¹ Requires the HP Smart app download. For details on local printing requirements see <http://www.hp.com/go/mobileprinting>. Certain features/software are available in English language only, and differ between desktop and mobile applications. Instant Ink subscription may be required. Instant Ink not available in all countries. See details at www.hpinstantink.com. Internet access required and must be purchased separately. HP account required for full functionality. List of supported operating systems available in app stores. Fax capabilities are for sending a fax only, and may require additional purchase. For more information, see <http://www.hpsmart.com/mobile-fax>. ² Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at <http://hp.com/go/mobileprinting>. Wi-Fi is a registered trademark of Wi-Fi Alliance®. ³ Based on monthly subscription cost of HP Instant Ink 700-page plans without purchase of additional sets of pages compared to cost per page to print ISO/IEC 24711 pages on most in-class, traditional A4 color inkjet cartridge printers & MFPs using original standard capacity cartridges priced for: Australia <299 AUD; New Zealand <349 NZD; Canada <=399 CAD & United States <399 USD. Sale prices not considered for this study. HP Ink Advantage printers excluded due to non-standard hardware & supplies model. Buyers Lab July 2020 study commissioned by HP, based on publicly available information as of June 1, 2020. Printers selected by market share in IDC Quarterly Hardcopy Peripherals Tracker - Final Historical 2020Q1. For details: www.keypointintelligence.com/HPInstantInk. ⁴ Based on internal HP testing. Average timing estimate based on: 1) downloaded HP Smart app on mobile or desktop device, 2) setting up Shortcut, 3) scanning jobs which have more than 2-3 tasks associated with them (scan to email, save and rename, store to cloud, etc.). Average timing savings comparison based on using printer and desktop scan software to complete similar scanning tasks. Requires the HP Smart app download and supported HP printer. For details on local printing requirements see <http://www.hp.com/go/mobileprinting>. ⁵ Compared to OEM printing apps for the majority of top-selling inkjet/laser printers and all-in-ones for the home and office, priced less than or equal to \$449.99 USD. Market share as reported by IDC CYQ4 2019 Hardcopy Peripherals Tracker. Claim based on research of printer manufacturer's print apps and Keypoint Intelligence - Buyers Lab hands-on testing and study commissioned by HP. For details, please see: <http://www.keypointintelligence.com/HPSmartApp>. ⁶ HP Instant Ink sign up required. HP Instant Ink not available in all countries. Subject to monthly page limit of plan selected. Must complete HP Instant Ink sign up within 7 days of setting up the printer with the HP-recommended setup process as indicated in the instructions that came with your printer. Use of in-box ink cartridge is included in period of offer. One offer redeemable per printer. Free months offer with HP Instant Ink subject to change after 10.31.2021. Offer cannot be redeemed for cash. Setup Offer may be combined with other offers; see terms and conditions of the other offer for more details. Requires a valid credit/debit card, an email address, and Internet connection to printer. Unless service is cancelled within the promotional period online at <http://www.hpinstantink.com>, a monthly service fee, based on the plan chosen, plus tax and overage fees will be charged to your credit/debit card. Customer will be charged for any overage fees and applicable taxes at the end of each month in the promotional period. See additional offer information available during online sign up process. For service details, see <http://www.hpinstantink.com>. ⁷ Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, host OS, port-monitor, software application, driver, and document complexity. ⁸ Based on plan usage, Internet connection to eligible HP printer, valid credit/debit card, email address, and delivery service in your geographic area. ⁹ Added value is calculated based on 6 months of any Instant Ink plan, up to \$24.99/month. See Instant Ink offer details on box (*) or at <http://www.hpinstantink.com>. With HP+, customers will also receive additional value in the form of one extra year of HP Carepack-based warranty and access to advanced HP Smart app features.

HP OfficeJet Pro 8025e All-in-One Printer w/ 6 months free ink through HP Plus Technical specifications

Functions / Multitasking supported	Print, copy, scan, fax / Yes
Print speed⁵	Letter: Up to 20 ppm; Black (ISO): Up to 20 ppm; Color (ISO): Up to 10 ppm; First page out black: As fast as 13 sec; First Page Out Color: As fast as 16 sec; Black (draft): Up to 29 ppm; Color (draft): Up to 25 ppm; Print speed Black Duplex: Up to 10 ipm; Print speed Color Duplex: Up to 7 ipm
Print resolution	Black (best): 1200 x 1200 rendered dpi; Color (best): Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Print technology	HP Thermal Inkjet
Print resolution technologies	HP Thermal Inkjet
Print cartridges number	4 (1 each black, cyan, magenta, yellow)
Borderless printing	Yes, on photo paper only, up to 8.5 x 11 in (US letter), 210 x 297 mm (A4)
Standard print languages	HP PCL3 GUI
Printer smart software features	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On
Scan type / Technology	Flatbed, ADF Contact Image Sensor (CIS)
Scan resolution	Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi
Scan file format	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
Scan input modes	Front-panel scan, copy, HP Software, EWS, Mobile apps
Scan size maximum	ADF: 8.5 x 14 in; Flatbed: 8.5 x 11.7 in
Scan speed	Up to 8 ppm (200 ppi, b&w), up to 3.5 ppm (200 ppi, color)
Bit depth / Grayscale levels	24-bit/ 256
Digital sending standard features	Scan to thumb drive/PC
Copy speed	Black (ISO): Up to 13 ppm; Color (ISO): Up to 7 ppm; Black (draft): Up to 29 ppm; Color (draft): Up to 23 ppm
Copy resolution	Black (text and graphics): Up to 600 dpi; Color (text and graphics): Up to 600 dpi
Maximum number of copies	Up to 99 copies
Copier settings	Number of Copies; Two-Sided; Lighter/Darker; ID Copy; Resize; Quality; Paper Size; Paper Type; Collate; Margin Shift; Crop; Copy Preview; Enhancements
Copier resize	25 to 400%
Fax resolution	Black (best): Up to 300 x 300 dpi; Color (best): 200 x 200 dpi; Black (standard): 203 x 98 dpi; Color (standard): 200 x 200 dpi
Fax speed	4 sec per page
Fax smart software features	Digital Fax - Fax to PC is available with Windows (Please use: Visit http://www.hp.com/support to download the latest software.
Fax Features	Fax memory: Up to 100 pages; Auto fax reduction supported: Yes; Auto-redialing: Yes; Fax phone features: Color fax; auto reduction; No answer redial; speed dial; Group speed dial; Junk fax blocker; Fax forwarding (black only); Distinctive ring; Delayed send (black only); Scan and fax; PC fax send and Fax to PC; Fax volume (off/soft/loud); CID; Fax delayed sending: Yes; Distinctive ring detection supported: Yes; Fax forwarding supported: Yes; Fax polling supported: No; Fax telephone mode supported: No; Junk barrier supported: Yes, requires Caller ID; Maximum speed dialing numbers: Up to 99 numbers; PC interface supported: Yes, PC fax send and archive; Telephone handset supported: No
Standard connectivity	1 USB 2.0; 1 Ethernet; 1 Wireless 802.11a/b/g/n; 1 RJ-11 Fax
Network capabilities	Yes, via built-in Ethernet; Wireless 802.11 a/b/g/n
Wireless capability	Yes, built-in WiFi 802.11 a/b/g/n
Mobile printing capability⁴	Chrome OS; HP Smart app; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ Certified
Memory	Standard: 256 MB; Maximum: 256 MB DDR3 SDRAM
Processor speed	1.2 GHz
Duty cycle⁷	Monthly, letter: Up to 20,000 pages
Recommended monthly page volume	Up to 800 pages
Media types supported	Plain Paper, HP Photo Papers, HP Matte Brochure or Professional Paper, HP Matte Presentation Paper, HP Glossy Brochure or Professional Paper, Other Photo Inkjet Papers, Other Matte Inkjet Papers, Other Glossy Inkjet Papers, Thick Plain Paper, Light/Recycled Plain Paper, HP Tri-fold Brochure Paper, Glossy
Media weight supported	16 to 28 lb (plain paper); 60 to 75 lb (photo); 20 to 24 lb (envelope); 90 to 110 lb (card)
Media sizes supported	Letter; Legal; Government Legal; Executive; Statement; 4 x 6 in; 5 x 7 in; 13 x 18 cm; 8 x 10 in; 10 x 15 cm; L; Photo 2L; Envelope (#10, Monarch, 5.5 bar); Card (4 x 6 in, 5 x 8 in)
Media Sizes Custom	Tray 1: 3 x 5 to 8.5 x 14 in
Paper handling	Input Capacities: Up to 225 sheets Standard; Up to 10 envelopes; Up to 60 sheets; Up to 225 sheets Legal Auto Document Feeder: Standard, 35 sheets Output Capacities: Up to 60 sheets Standard; Up to 10 envelopes; Up to 10 sheets; Up to 60 sheets Legal Duplex Options: Automatic (standard) Envelope feeder: No Standard paper trays: 1

What's in the box⁸	1K7K3A HP OfficeJet Pro 8025e All-in-One Printer; HP 910 Setup Black Instant Ink Ready Cartridge; HP 910 Setup Cyan Instant Ink Ready Cartridge; HP 910 Setup Magenta Instant Ink Ready Cartridge; HP 910 Setup Yellow Instant Ink Ready Cartridge; User Guide; Setup poster; Power cord [For ink volume and page yield information, visit hp.com/go/learnaboutsupplies]
Replacement cartridges	HP 910 Black Original Ink Cartridge (~300 pages) 3YL61AN; HP 910 Cyan Original Ink Cartridge 3YL58AN; HP 910 Magenta Original Ink Cartridge 3YL59AN; HP 910 Yellow Original Ink Cartridge 3YL60AN (CMY composite ~315 pages); HP 910XL Black Original Ink Cartridge (~825 pages) 3YL65AN; HP 910XL Cyan Original Ink Cartridge 3YL62A; HP 910XL Magenta Original Ink Cartridge 3YL63A; HP 910XL Yellow Original Ink Cartridge 3YL64AN (CMY composite pages ~825); HP 916XL Black Original Ink Cartridge 3YL66AN (~1,500 pages). Actual yield varies considerably based on content of printed pages and other factors. For details see http://www.hp.com/go/learnaboutsupplies
Instant ink eligible	HP Instant Ink eligible / Save up to 50% on ink. For more information visit http://www.hpinstantink.com
Product dimensions	W x d x h: 18.11 x 13.43 x 9.21 in; Maximum: 18.12 x 20.13 x 9.17 in
Product weight²	18.04 lb
Warranty features	One-year limited hardware warranty; 24-hour, 7 days a week Web support; business hour phone support within warranty period.
Energy efficiency compliance	EPEAT® Silver
Energy star certified	Yes
Control panel	2.7" (6.86 cm) touchscreen control panel with CGD (color graphic display); 3 buttons: (home, help, back)
Display description	2.7" (6.86 cm) Capacitive Touchscreen CGD (Color Graphic Display)
Software included	HP Printer Software, Shop for Supplies Online
Compatible operating systems	Windows 10, 8.1, 8, 7, Windows Server 2008 R2 64-bit, Windows Server 2008 R2 64-bit (SP1), Windows Server 2012 64-bit, Windows Server 2012 R2 64-bit, Windows Server 2016, Chrome OS
Compatible network operating systems	Windows 10, 8.1, 8, 7: 32-bit or 64-bit, 2 GB available hard disk space, Internet connection, Internet Explorer, OS X v10.11 El Capitan; macOS Sierra v10.12 (previously OS X); macOS High Sierra v10.13; 1.5 GB available space; Internet access Linux (For more information, see http://hplipopensource.com/hplip-web/index.html), Chrome OS
Minimum system requirements	PC: Windows 10, 7: 32-bit or 64-bit, 2 GB available hard disk space, Internet connection, Internet Explorer.; Mac: macOS v10.14 Mojave, macOS v10.15 Catalina, macOS v11 Big Sur; 2 GB HD; Internet required
Power³	Power supply type: Internal (Built-in) Universal Power Supply; Power requirements: Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz; Power consumption: Up to 21 watts (printing), 5.80 watts (ready), 1.00 watts (sleep), 0.08 watts (manual-off)
Acoustics	Acoustic power emissions: 6.8 B(A) (printing at 16 ppm); Acoustic pressure emissions: 62 dB(A) (printing at 17 ppm)
Operating environment	Operating temperature range: 41 to 104°F; Recommended operating temperature: 59 to 90°F; Storage temperature range: -40 to 140°F; Operating humidity range: 20 to 80% RH; Recommended humidity operating range: 20 to 75% RH
Accessories	None
HP Service and Support options	HP Support Center (Online Web support); Print Scan Doctor

Learn more at hp.com

¹ Dimensions vary as per configuration ² Weight varies as per configuration ³ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. ⁴ Wireless performance is dependent upon physical environment and distance from the access point. Wireless operations are compatible with 2.4 GHz routers only; excludes wireless direct. Wireless direct may require driver or apps be installed and connected on wireless-enabled mobile device or PC. Wireless functionality may vary by computer and mobile operating systems, see <http://hpconnected.com>. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. AirPrint supports OS X v10.11 El Capitan and devices running iOS 4.2 or later and requires the printer be connected to the same network as your OS X or iOS device. AirPrint, the AirPrint Logo, iPad, iPhone, and iPod touch are trademarks of Apple® Inc. Windows is a trademark of the Microsoft group of companies. ⁵ Speed specifications have been updated to reflect current industry testing methods. ⁶ Either after first page or after first set of ISO test pages. For details see <http://www.hp.com/go/printerclaims> ⁷ HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement. ⁸ For more information about page yields for replacement cartridges see <http://hp.com/go/learnaboutsupplies> for setup cartridges click on Setup supplies link on the same page.

