# **Product data sheet**

Specifications



APC NetShelter Rack PDU Advanced, Switched, 3Phase, 8.6kW, 208V 30A, 48 Outlets, L21-30P

APDU10351SW

### Overview

Lead time Usually in Stock

#### Main

Color	Black
	DIAUK
Product or Component Type	PDU
PDU Type	Switched
Cord length	5.9 ft (1.8 m)

### Complementary

Input Voltage	208 V 3 phase	
Height	70.08 in (178.0 cm)	
Width	2.2 in (5.6 cm)	
Output Voltage	208 V	
Depth	3.0 in (7.5 cm)	
Net Weight	20.7 lb(US) (9.4 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	NEMA L21-30P	
Mounting Mode	Rack-mounted	
Rack units	0U	
Mounting position	Vertical	
Communication Port Protocol	1000BASE-T 10/100BASE-T	
Line Rated Current	24 A	
Acceptable Input Voltage	200240 V	
Input current limits	30 A	
Load Capacity	8600 VA	
Input Frequency	50/60 Hz	
Outlet type and quantity	24 C13/C15/C19/C21 24C13/C15	

#### **Environment**

Product Certifications TAA compliance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	UL 62368-1 CSA C22.2 No 62368-1 FCC part 15 Subpart B	
IP Degree of Protection	IP44	
Ambient Air Temperature for Operation	23140 °F (-560 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	0 50000 ft (0 000000000 15240 000000000 m)	

# Ordering and shipping details

GTIN	731304439806
Country of origin	US

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	78.0 in (198 cm)
Package 1 Width	4.6 in (11.6 cm)
Package 1 Length	8.2 in (20.8 cm)
Package 1 Weight	27.3 lb(US) (12.4 kg)

## **Contractual warranty**

Warranty 3 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information