



## W2050 Pro 1080p Auto Focus Webcam

Part Number: K81176WW | UPC Code: 085896811763

Showcase you,  
your team, or your  
background.

The technological and software knowledge needed to create an optimized video conferencing setup can be overwhelming. Professionals require a solution that simplifies their experience. Kensington's W2050 Pro 1080p Auto Focus Webcam provides a wide 93° field of view to accommodate team meetings, lectures, and product presentations, and adds the professional touch to today's video conferencing applications, including Microsoft Teams, Google Meet, Zoom, and more. Delivering high-quality video (1080p @ 30fps), dynamic 2x zoom, two omnidirectional stereo microphones, flexible camera placement, and enhanced low light imaging, the W2050 elevates your video conferencing experience.

Features include:

- Optimized for Microsoft Teams, Zoom, and more
- Wide 93° field of view accommodates multiple participants
- Personalize video settings with Kensington Konnect™
- Electronic pan, tilt, and 2x zoom for focal point changes
- Manually moves 37° vertically and 360° horizontally
- Large sensor size for low light imaging
- Omnidirectional microphone with noise cancellation
- Rigorously tested and approved for wipe down protection




## W2050 Pro 1080p Auto Focus Webcam

Part Number: K81176WW | UPC Code: 085896811763



### Professional Video Technology

Delivers high-quality video at 1080p (1920x1080/30fps)—with automatic focus and large sensor for enhanced low-light performance.



### Simple & Powerful Software

Customize your video settings with the click of a button. Use Kensington Konnect™ to optimize your focus, lighting, and experience in any setting.



### Wide Video Frame with Privacy

The 93° diagonal field of view is ideal for team meetings, lectures, or presenting products. The integrated lens cover allows you to control when you are seen.




### Versatile Positioning

Manually adjust your webcam up to 37° vertically and 360° horizontally to ensure the best camera angles. Take control with electronic pan, tilt, and 2x zoom (ePTZ) to showcase you, your products, or your team.



### Omnidirectional Stereo Microphones

Two microphones with noise-reduction technology ensure you sound professional in every meeting and presentation.



### Kensington Ecosystem Compatible

Create a tailored setup based on your environment and budget by combining with a Desktop Stand (SKU code: K87651WW), Ring Light (SKU code: K87653), or other Kensington video conferencing accessory.

# W2050 Pro 1080p Auto Focus Webcam

Part Number: K81176WW | UPC Code: 085896811763

## Wipe Down

Meets MIL-STD-810H Method 504.3 Contamination by Fluids testing for resistance to breakdown when exposed to cleaning and disinfecting solvents such as alcohol and bleach for at least 24 hours.

## System Requirement

Operating Systems Supported	Windows 10 or later; macOS 10.15 or later; Chrome OS
Plug & Play	Yes
Software	Kensington Konnect: Download from Kensington website ( <a href="http://www.kensington.com/konnect">www.kensington.com/konnect</a> )

## USB Connections

Cable	1.5m (5') USB-A Cable with USB-A to USB-C Adapter
-------	---

## Microphone

Type	Omnidirectional Stereo microphone (Dual)
------	--

## Camera

Megapixels	2
CMOS Sensor Size	1/2.7"
FOV	93° diagonal
Focus	Autofocus
Privacy Cover	Yes
Mounting	1/4" thread mount, Mounting Clip

## LED Indicator

RGB	Blue LED indicates Webcam is on
-----	---------------------------------

## Material Specifications

Main Frame	ABS
Front Cover	ABS
Rear Cover	ABS
Camera Cover	ABS+Nickel Plating
Camera Lens	Plastic
LED Light Guide	PC
Cable	TPE
Clip Stand Base	ABS
Clip Rubber	TPU
Clip Lift Base	ABS

# W2050 Pro 1080p Auto Focus Webcam

Part Number: K81176WW | UPC Code: 085896811763

Clip Lift Rubber Upper	Silicon Rubber
Clip Lit Rubber Bottom	Silicon Rubber
1/4" Insert Nut	Copper alloy
Hinge Screw	SUS304

## Product Dimensions

Unit Dimensions	Width: 89mm (3.50") Length: 48mm (1.88") Height: 53.7mm (2.11")
Unit Weight	0.27lbs (125g)
Enclosure Color & Material	Black / ABS
Desktop Footprint	47.8 cm <sup>2</sup>

## Packaging Dimensions

Packaging Style	Retail Sleeve Box
Packaging Dimensions(Unit)	Width: 6.04in (153.5mm) Length: 6.38in (162.1mm) Height: 3.01in (76.5mm)
Packaging Weight(Unit)	0.66lbs (0.3kg)
Packaging Content	Webcam, USB A-to-C adapter, Compliance Sheet, Warranty, Welcome insert, China RoHS Sheet
Master Carton	8 pcs

## Power & Environmental

Power Imaging	No
Power Standby	5V/0.04A 0.2W
Power Adapter Rating	5V/200mA 1W
Operating Temperature	0 to 40°C (32 to 104°F)
Storage Temperature	-15 to 65°C ( 5 to 149°F)
Relative Humidity	55% operating temperature @ 25°C

## Country of Origin, Regulatory, and Warranty

Country of Origin	China
Certifications & Compliance	FCC, IC, CE, UKCA, RCM, VCCI, IEC/EN 62368-1, EU REACH, RoHS/WEEE, ACCO RSL
Warranty	2-Year Worldwide



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2021 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k20-20234p

**Kensington**

The Professionals' Choice™