

TR-MRP08-B / TR-MRP082T-B

Network Video Recorder with Turing Vision Bridge



Key Features

- ✓ Turing cloud-ready with Smart NVR series and Turing bridge/servers
- ✓ Support Ultra265/H.265/H.264 video formats
- ✓ 8-channel Plug and Play POE input
- ✓ Support HDMI and VGA simultaneous output
- ✓ Up to 8MP input resolution
- ✓ 2 SATA HDDs, up to 10TB for each HDD



SPECIFICATIONS

Network	
Incoming Bandwidth	80Mbps
Outgoing Bandwidth	64Mbps
Remote Users	128
Protocols	P2P, UPnP, NTP, DHCP, PPPoE

VIDEO/AUDIO	
IP Video Input	8-ch
Two-way Audio Input	1-ch, RCA
HDMI/VGA Output	HDMI: 1920X1080@60, 1920X1080@50, 1600X1200@60, 1280X1024@60, 1280X720@60, 1024X768@60 VGA: 1920X1080@60, 1920X1080@50, 1280X1024@60, 1280X720@60, 1024X768@60
Recording Resolution	8MP/6MP/5MP/4MP/3MP/1080p/960p/720p/D1/2CIF/CIF
Audio Output	1-ch, RCA
Synchronous Playback	8-ch
Corridor Mode Screen	3/4/5/7/9

Decoding	
Decoding Format	Ultra 265, H.265, H.264
Live View Playback	8MP/6MP/5MP/4MP/3MP/1080p/960p/720p/D1/2CIF/CIF
Capability	2 x 4K@30, 4x 4MP@30, 5 x 3MP@30, 8 x 1080P @30

Hard Disk	
SATA	2 SATA interface
Capacity	Max 10TB per disk
Bundled HDD	TR-MRP08-B: None TR-MRP082T-B: 2TB

External Interface	
NETWORK INTERFACE	1 RJ45 10M/100M/1000M self-adaptive Ethernet Interface
USB Interface	Front panel: 1 x USB2.0, Rear panel: 1 x USB3.0
Alarm In	4-ch
Alarm	1-ch


PoE	
Interface	8 RJ-45 10M/100M self-adaptive Ethernet Interface
Max Power	Max 30W for single port Max 130W total
Supported Standard	IEEE 802.3af/at

GENERAL	
Power Supply	100 ~ 240 V AC Power Consumption: ≤10W(without HDD)
Working Environment	-10°C~+ 55°C (+14°F~+131°F), Humidity ≤ 90% RH (non-condensing)
DIMENSIONS	380mm × 315mm × 53mm (14.9" × 12.4" × 2.1")
NET WEIGHT	≤2.6kg (5.73lb)

COMPATIBILITY	
ONVIF	Profiles S/G/T
Recommended Turing Cameras	SMART Series Only



DIMENSIONS



REAR PANEL

