


PE10ZJ-OS-45P0D

PoE is a technology that lets network cables carry electrical power and delivery is intelligent, and designed to protect network equipment from overload, underpowering. GVision's 10.1" PoE monitor is built-in Android OS and design for run 24 / 7 operation. It's support 10-points projected capacitive PCAP touch technology screen for the industry where it requires touch capability.

DIMENSIONS

Unit: Inch



FEATURES

- 10.1-Inch Screen Size / 1280 x 800 Resolution
- Ethernet 10/100 RJ45 PoE Port Input Interface
- Built-In ANDROID 10 Operating System
- 10-Points PCAP Projected Capacitive Touch Technology
- I/O Ports: Mini HDMI / USB Type-C / RJ45(PoE) / USB2.0 / USB3.0
- 350 nits High Brightness / LED Direct Backlight Unit
- 170° / 170° Wide Viewing Angle
- 24 / 7 Operation Design
- 3-Year Warranty

SPECIFICATIONS

DISPLAY		PE10ZJ-OS-45P0D
Screen Size	10.1 In	
Resolution	1280 x 800	
Display Area	216.96(H) x 135.6(V)	
Backlight	LED Direct	
Aspect Ratio	16 : 10	
Viewing Angle	170° / 170°	
Response Time	25ms	
Brightness	350cd/m²	
Contrast Ratio	800 : 1	
Color Depth	16.7M	
INTERFACE		
Mini HDMI In	1	
RJ45 (PoE)	1	
USB 2.0 / 3.0	1 / 1	
USB Type-C	1	
Earphone Out	1	
TOUCH		
Type	Projected Capacitive PCAP	
Points	10-Points	
Surface Hardness	7H	
SYSTEM		
OS	Android 10	
RAM/ROM	4GB / 32GB Flash	
Network	WiFi	
CABINET		
Material	Metal	
POWER		
Consumption	< 15W	
Saving Mode	< 1W	
Type Input	RJ45 PoE	
TEMPERATURE		
Operating	32° F ~ 122° F (0° C ~ 50° C)	
Storage	-4° F ~ 140° F (-20° C ~ 60° C)	
DIMENSIONS (WxHxD)		
Inch (in)	9.83 x 6.62 x 1.18	
Millimeter (mm)	249.8 x 168.4 x 30.0	
WEIGHT		
Net Weight	7.7 lbs (3.5 kg)	
VESA™		
Mount Size (mm)	75 x 75	
PACKAGE CONTENTS		
Accessoaries	Power cable and power adaptor	

Specifications subject to change without any notice