



Planar MGP Complete 217

LED Video Wall Display

Planar® MGP Complete™ 217 is a Full HD, 217" LED video wall solution that includes everything an organization needs to deliver large-format beautiful video and imagery, in less time and with less effort. The solution comes with LED display cabinets, cables, spare modules, wall mounts and full-featured video controller all included. The ADA-compliant Planar MGP Complete 217 features front-side installation and serviceability for easier access and installation against the wall.



SPECIFICATION	DETAIL
Part Number	998-2869-00
Planar Model	MGP217
Pixel Pitch	2.5
Display Diagonal	216.8in
Display Resolution	1920x1080
Pixel Density	160,000/m ² 14,862/ft ²
Display size	4800 x 2700 x 50mm 188.98 x 106.3 x 1.97in
Power Consumption, Maximum (watts)	7037
Line Voltage	100-240V AC, 50/60Hz
Display Weight	444.2kg 979.29lbs
Brightness	600
Contrast Ratio	5000:1
LED Refresh Rate	3840Hz
Color Temperature, Adjustable (k)	3,000 - 10,000

Video Inputs	1x HDMI, 1x DVI
Control	USB, Serial, Network
Frame Rate	50, 60Hz
Viewing Angle, Horizontal	160°
Viewing Angle, Vertical	140°
Service Access	Front, Rear
Environment	Indoor
Operating Temperature/Humidity (degrees F/C, relative humidity)	-20° to 40° C -4° to 104° F 10-80%
Storage Temperature/Humidity (degrees F/C, relative humidity)	-30° to 60° C -22° to 140° F 10-85%
LED Lifetime (Half Brightness)	100,000 hrs
Solution Includes	Video Wall display, Video controller, signal cables, power cables, wall mount, and spare modules
Warranty	3 years; 24-hour customer service
HDMI®	Planar utilizes HDMI® standards in this product. The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI Trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 2/13/2024

© Copyright 2024 Planar Systems, Inc. All rights reserved