

ExpertBook B5 Flip | B5402F

Power to turn your business world

ASUS ExpertBook B5 Flip is built for business success in style, with a precision-crafted chassis that pushes the limits of lightness — plus a 360° flippable design and a garaged stylus for ultimate flexibility. Powered by cutting-edge 11th Gen Intel® Core™ processor. ExpertBook B5 Flip is your perfect portable, powerful partner for the corporate world.





CPU



Ultra light



- Lightweight from 1.38 kg
- Aluminum and Mg-Al alloy chassis
- Up to 10hrs of long battery life, support fast charging





All-day battery

360° EgoLift hinge

Exceptional performance for Business

- Up to 11th Gen Intel CoreTM i7 processor with **Iris X**^e graphic
- Dual SSD up to **2TB** support Raid 0, Raid 1*
- Up to 48 GB DDR4 3200MHz Memory
- Full I/O ports with Thunderbolt[™] 4, HDMI, USB type-A, RJ45 and microSD card
- Two-way Al noise-canceling technology with hot key



Al noise-canceling technology



Garaged stylus

Business Focus Design

- Up to WiFi 6E* & ASUS WiFi Master provides seamless connection
- 360° flip design with garaged MPP 2.0 stylus to conquer every using scenario
- User-status indicator on the top cover
- ASUS exclusive NumberPad*



US military grade





Dual SSDs Support RAID 0, 1

Enterprise-grade durability and security

- **US Military Grade** durability to cope with business rigors on the road
- IR Camera* for facial log in and webcam shield
- TPM 2.0 chip*, Kensington lock slot, fingerprint sensor

Warranty and Support



3-Year global warranty

100% free of charge, with no hidden costs.



Pick Up & Return service

Enjoy a door-to-door service including pick up, repair, and return.



MyASUS App

Contact customer service, view repair status, read product guides and more.

^{*} Optional specification

SPECIFICATION







Model	B5402F
Operating system	Windows 11 Pro(ASUS recommends Windows 11 Pro) Windows 11 Home
CPU	Intel® Core™ i7-1195G7 processor 2.9 GHz (12MB cache, up to 5.0 GHz, 4 cores) Intel® Core™ i5-1155G7 processor 2.5 GHz (8MB cache, up to 4.5 GHz, 4 cores)
GPU	Intel® Iris Xe graphics
Memory	1 x onboard, 1 x SO-DIMM, up to 48 GB DDR4 3200 MHz Onboard: 4 GB/8 GB/16 GB DDR4 3200 MHz SO-DIMM: 4 GB/8 GB/16 GB/32 GB DDR4 3200 MHz
Storage	2 x M.2 SSD, up to 2 TB PCle® 3.0 SSD 256 GB/512 GB/1 TB M.2 PCle®3.0 Value SSD 1 TB M.2 PCle®3.0 Performance SSD
Display	14.0" FHD (1920 x 1080), IPS, 16:9, touch screen, wide view, anti-glare, 400 nits, stylus support, 100% sRGB 14.0" FHD (1920 x 1080), IPS, 16:9, touch screen, wide view, anti-glare, 400 nits, stylus support, low power, 72% NTSC
Stylus	MPP 2.0 garaged stylus
I/O ports	2 x Thunderbolt™4 Type-C (supports 4K display, USB PD3.0), 1 x USB3.2 Gen2 Type-A 1 x USB2.0 Type-A, 1 x HDMI 1.4b, 1 x microSD card reader 1 x 3.5 mm combo audio jack, 1 x RJ45, 1 x Kensington Nano Security Slot
Video camera	1.0 MP camera with 720 P HD video, Webcam Shield IR camera with 720 P HD video, Webcam Shield
Wireless	Dual-band 2x2 WiFi 6E + Bluetooth® 5.2 Dual-band 2x2 WiFi 6 (802.11ax) + Bluetooth® 5.2
Audio	2 x speaker 2 x multi-array microphone ASUS two-way AI Noise-Canceling Technology Cortana voice-recognition support
Weight	Starting at 1.38kg
Dimensions (WxDxH)	32.34 x 22.31 x 1.79 cm
Battery	63 Wh, 3-cell, Li-polymer
Security	Fingerprint sensor(combo power button), TPM 2.0 (optional), IR Camera (optional), Webcam Shield , Kensington lock slot
Keyboard and touchpad	Full-size keyboard with 1.5 mm key travel; backlit (optional); spill-resistant to 66cc* *Quantity used during testing, with duration of 3 minutes
NumberPad	Optional
Featured software	ASUS Control Center (sold separately), ASUS Business Manager, MyASUS
AC adapter	USB Type-C®, 65 W; Output: 20 V DC, 3.25 A; Input: 100~240 V AC 50/60 Hz universal
Energy efficiency compliance	Energy star, EPEAT

Disclaimer:

1. ASUS Expert Series Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.

Recommended Accessories



ASUS SimPro dock 2



ZenScreen MB165B



65W USB-C Ultra Mini Universal Adapter