



MAINSTREAM COMPUTING FOR A VARIETY OF BUSINESS USES



ThinkCentre M8 Series desktops offer enhanced manageability and security features, along with additional configuration and expansion options.

ThinkCentre M80s

Smarter
technology
for all

Lenovo

Offers almost the same performance capabilities of a larger desktop, but in a smaller chassis, thanks to the efficient cooling system which improves air-flow. Features 10th Gen Intel Core processors, support for vPro remote manageability to reduce the cost of IT maintenance, space to install up to 3 storage devices (1x M.2 PCIe SSD and 2x HDD), an optical drive and a graphics card.



REASONS TO BUY

Security features include an optional Chassis eLock which locks the computer from the inside preventing unauthorized removal of components, a cable retention system preventing removal of wired peripherals, and the ability to disable individual USB ports or prevent data transfer through them.

Despite its smaller size, users can connect 3 displays without needing a graphics card - ideal for users multi-tasking across applications.

Optimized to reduce power consumption, saving you money and reducing environmental impact. Features Energy Star and EPEAT Silver certifications. TUV low noise and TCO certified for lower cost of ownership.

ThinkCentre M80s

KEY SPECIFICATIONS

Processor	up to 10th Gen Intel Core i9 processor
Operating System	Powered by Windows 10 Pro
Graphics	Intel HD Graphics 630/610 in processor, optional AMD Radeon 520
Memory	up to 128GB DDR4-2933
Storage	Internal storage: up to 1x 3.5" 2TB SATA HDD + 1x 2.5" 1TB SATA HDD or 2x 2.5" 256GB SATA SSD M.2 SSD: up to 1x 1TB M.2 PCIe NVMe optional Intel Optane memory
Optical	optional DVD-ROM or DVD burner
Additional Internal Bays	Optional 2.5" Bay
Expansion Slots	PCIe x16, low profile PCIe x1, low profile 2x brackets for optional port extensions
Power Supply	One of the following 180W 85% 260W 85% 310W 92% 380W 92%
Dimensions	Width: 93mm (3.6") Depth: 298mm (11.7") Height: 340mm (13.4")
Weight	starting at 5.3kg (11.7lb)

GREEN CERTIFICATIONS

EPEAT Silver, Energy Star 8.0

OTHER CERTIFICATIONS

TUV Ultra Low Noise, TCO Certified.

CONNECTIVITY

Front I/O	2x USB 3.2 Gen 2, 2x USB 3.2 Gen 1, 1x USB-C 3.2 Gen 1 (15W charging), microphone (3.5mm), audio combo jack (3.5mm)
Rear I/O	4x USB 3.2 Gen 1, serial (9-pin), ethernet (RJ-45), 2x DisplayPort*, 1x HDMI*, line-out (3.5mm) [*integrated graphics models]
Optional Rear Ports	One of the following 1x parallel 1x parallel + 1x serial 1x parallel + 5x serial 1x serial 1x serial + 2x USB 2.0 1x serial + 4x USB 3.2 Gen1 2x PS/2 2x PS/2 + 1x parallel + 1x serial 2x PS/2 + 2x USB 2.0 + 2x USB 3.2 Gen1 2x USB 2.0 2x USB 2.0 + 2x USB 3.2 Gen1 2x USB 3.2 Gen1 4x USB 3.2 Gen1 + 1x serial + 2x PS/2 4x USB 3.2 Gen1 + 2x USB 2.0 + 1x serial 4x serial
WLAN + Bluetooth	One of the following Intel 9560 11ac, 2x2 + BT5.0 Intel AX201 11ax, 2x2 + BT5.1, vPro RTL8822CE 11ac, 2x2 + BT5.0
Ethernet	One of the following BN8E88 + Integrated 100/1000M I350-T4 + Integrated 100/1000M Integrated 100/1000M

SECURITY & PRIVACY

Chassis Intrusion Switch

E-Lock
Kensington lock slot
Padlock slot
Optional Smart Cable Clip
Smart USB protection
Individual USB port disablement
Hardware TPM 2.0

MANAGEABILITY

Intel vPro
Non-vPro

Recommended for this device



ThinkVision P24q-20

23.8" QHD (2560x1440) monitor with 99% sRGB colour gamut

1x HDMI, 1x DisplayPort (in), 1x DisplayPort (out), 4x USB3.1, 1x USB 3.1 Type-B upstream, audio out

Lift, Tilt, Pivot, Swivel stand for viewing comfort. Integrated smartphone holder in base.



ThinkVision T24h-20

23.8" QHD (2560x1440) near-borderless monitor with 99% sRGB color gamut and anti-glare coating

1x HDMI, 1x DisplayPort, 1x USB-C, 4x USB3.1, audio out

Lift, Tilt, Pivot, Swivel stand for viewing comfort. Integrated smartphone holder in base.



Premier Support

Talk directly with advanced technical support agents

Support for software & hardware

Next business day onsite repairs