

# HP ScanJet Enterprise Flow N6600 fnw1 (20G08A)



## Boost productivity for professional scanning tasks with the fast, reliable, network connected HP ScanJet Enterprise.

Boost productivity for professional scanning tasks with the fast, reliable, network connected HP ScanJet Enterprise, designed for scanning up to 8,000 pages daily. Automate workflows with shortcuts and fast, two-sided scanning from the document feeder.



### **Ultimate Productivity.**

Scan up to 100 images (50 pages) per minute with a 100-page, two-sided, single-pass auto document feeder.[1]

### **Easy to use.**

Scan a variety of documents including books, magazines, and ID cards from the ADF or the Legal-size flatbed.

### **Ultimate Reliability.**

Capture every page easily, HP EveryPage technology uses ultrasonic sensing to separate pages in the ADF.

## **Featuring**

Get scan jobs done blazing fast [1]

Capture every page, every time

Versatile scanning

Simple scan to USB drive

Fast, versatile connectivity [3]

No waiting - Instant on [2]

## Specifications

<b>Scanner advanced features</b>	One pass duplex scanning; Multi-feed detection sensor; Configurable Scan shortcuts with HP Scan Premium Software: OCR; Auto exposure; Auto threshold; Auto detect colour; Background smooth/removal; Auto detect size; Straighten content; Enhance content; Auto orient; Multicolour dropout; Edge erase; Blank page options: Delete Blank Page, Blank Page Detection Sensitivity, Zonal Blank Detect; Merge pages; Document separation options: Zonal Text Separation, Barcode Separation, Blank Page Separation, Detect All/ Exclude All Edges Evenly/Exclude Edges Specifically, HP Separator Page Separation, Barcode Settings for Doc Separation, Any Format/Specific Format, Barcode Value, Delete Barcode Separator; Auto Feed; Show Viewer After Scan and Post Scan Operations are: Mark the image for Deletion, Rotate option, Move Left/Right, Create/Delete New Selection, Save as Scan Area, Manual Straighten option, Drag and Crop, Undo Options, image - Basic Zoom Slider, Open in Zoom Window (Zoom, Crop, Rotate) ; Background Clean-up options: Clean-up Background, Remove: make white, Smooth, make consistent, Remove Holes; Multi-Streaming; Multizone Selection for Zonal OCR, Barcode and QR Code; Multizone options: Ability to select Multiple Zones for OCR/Barcode, File Naming, Folder Naming, Document separation, Capture Metadata; Digital Stamp; PDF options: PDF Security Settings (Applicable for PDF and Searchable PDF), Password Security & Document Permission Settings, PDF – iHQC compression, File Size/Quality Slider, PDF Digital Signature; TIFF Compression Options: for Gray or Color: Uncompressed/LZW/Jpeg-Tiff, for BW: Uncompressed/LZW/Tiff G3/Tiff G4; File Name Options: Base Name, Date, Time, Batch Counter, Document Counter, Barcode Value, Zonal Text, File name sequence Settings, If File name already exists Actions - Overwrite/Append Date Time Stamp/Prompt for File Name, Intelligent File Naming; Destinations options: Email (Mail Clients, Save Local Copy Option, Local or NW), Folder, Save Folder path, Show Save as Dialog Box, After Saving the File(s) action, Printer/Fax, Send To multiple Destinations, Custom Destinations, Sub Folder Name by Date of Scan, by Time of Scan, Plugins available if not already included: SMTP, SFTP, Box and Evernote, SharePoint, SharePoint365, Google Drive, Dropbox, OneDrive, One Drive for Business and more.; XML and PDF Metadata; Enable Book Scan (Flatbed); Intelligent Document Classification; Manual Redaction; Vertical Streak Removal/Detection; Multi Document Scanning; Enable Desktop Icons creation for Scan Profiles/Shortcuts; Shortcut Management: Create new Scan Shortcut, Delete, Rename, Move Up/Down, Save/Undo, Restore Defaults-Factory Settings, Import/Export Shortcuts, retrieve shortcuts from Scanner without accessing the software on the PC; Configurable Scan shortcuts as standalone (using only the firmware of the scanner) without using the HP Scan Software: Scan to Computer, E-mail, Network Folder, SharePoint, Scan to USB Drive.
<b>Connectivity, standard</b>	Ethernet 10/100/1000 Base-T, USB 3.0, WiFi 802.11 b/g/n, WiFi Direct
<b>Network protocols, supported</b>	Via built-in networking solution: TCP/IP, IPv4, IPv6; Web Services; Discovery: Bonjour, Web Services Discovery; IP Config: IPv4 (DHCP, Manual), IPv6 (DHCPv6) ARP;ICMP; IGMP;UDP;TCP;DHCP;APIPA;DNS;mDNS;LLMNR;WSD;WS-Scan;SNTP;SMB;SNMP;FTP;SFTP;SMTP;HTTP Server Part;HTTPS
<b>Software included</b>	HP Scan Premium Software, HP Scanner Device Driver, HP WIA scan driver, HP TWAIN scan driver, HP Scanner Tools Utility, ISIS driver
<b>Compatible Operating Systems</b>	Windows 11; Windows 10; Windows 8; Windows 8.1; Windows 7; Windows Server; macOS 10.14 Mojave; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Linux
<b>Energy star certified</b>	Yes
<b>Ecolabels</b>	CECP; SEPA; IT ECO Declaration; EPEAT® Silver registered <sup>[1]</sup>
<b>Digital sending standard features</b>	Send to email (Store up to 50 e-mails); Send to network folder; Send to PC
<b>Digital sending optional features</b>	Send to email; Send to network folder; Send to PC
<b>Scan file format</b>	For text and image pages : PDF, JPEG, PNG, BMP, TIF, Text(TXT), Rich Text(RTF), SEARCHABLE PDF, PDF/A, Word(DOC), Word(DOCX), Excel(XLS), Excel(XLSX), CSV, XML
<b>Scan input modes</b>	Scan front-panel function : Scan to Computer, Scan to E-mail, Scan to Network Folder, Scan to Share Folder, Scan to USB Drive and Everyday Scan. HP Scan in Win OS, HP Easy Scan/ICA in Mac OS and THIRD parties applications via TWAIN.
<b>Scan technology</b>	ADF; Flatbed; Contact Image Sensor (CIS)
<b>Scanner type</b>	ADF; CIS scanning technology; Flatbed
<b>Display</b>	2.8-in (7.11-cm) Touchscreen
<b>Minimum dimensions (W x D x H)</b>	536.5 x 325.4 x 133.3 mm
<b>Minimum dimensions (W x D x H)</b>	21.1 x 12.8 x 5.2 in
<b>Weight</b>	6.1 kg
<b>Weight</b>	13.4 lb
<b>Power consumption</b>	23.9 watts (Active - Scanning), 7 watts (Ready), 2 watts (Sleep), 0.06 (Auto-Off), 0.06 (Manual-Off) (Power requirements are based on the country or region where the product is sold. Do not convert operating voltages or use with other voltages. Doing so might cause damage that would not be covered under HP product warranty.)
<b>Power supply type</b>	External power adapter
<b>What's in the box</b>	HP ScanJet Enterprise Flow N6600 fnw1 Scanner; Install guide; Supporting flyers; Cushions; USB cable; Power adapter; Power cords

---

**Manufacturer Warranty**

One-year limited hardware warranty, phone and Web support included. Warranty may vary by country as required by law. Go to <http://www.hp.com/support> to learn about HP world-class service and support options in your region.

---

## Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

## Messaging Footnotes

[1] Scan speeds measured at 300 dpi (black and white, grayscale, and color). Actual processing speeds may vary depending on scan resolution, network conditions, computer performance, and application software.

[2] Compared with products that use traditional fusing and cold cathode fluorescent lamp (CCFL) copying.

[3] Wireless performance is dependent on physical environment and distance from access point, and may be limited during active VPN connections.

## Technical Specifications Footnotes

[1] EPEAT® Silver registered where applicable. EPEAT registration varies by country. See <http://www.epeat.net> for registration status by country.

---

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

