



# PXV2410

## 24" Full HD video conferencing monitor

The slim Planar® PXV2410 is a 24" Full HD video conferencing monitor that features a built in 2MP webcam, microphone and speakers that support Windows Hello. A shutter slider ensures privacy and prevents accidental appearances on camera. An ergonomically-designed stand with height adjustment, pivot, swivel and tilt provides end user comfort while the built-in USB hub allows home, office or healthcare users to conveniently connect devices. As an added feature, one of the USB 3.0 ports provides BC1.2 and can power devices up to 1.5A.



SPECIFICATION	DETAIL
Product Name	PXV2410
Planar Part Number	998-2946-00
Viewable Size	23.8" diagonal (20.75" horizontal x 11.67" vertical)
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	178° Horizontal and Vertical
Response Time (typ)	6 ms (GTG)
Brightness (Typical)	250 cd/m <sup>2</sup>
Display Type	IPS LCD Active Matrix Flat Panel Display (TFT)
Display Resolution	Full HD 1080P, 1920 x 1080
Tilt Range	-5° to +20°
Palette	16.7 million colors
Pixel Pitch	0.2745 mm
Refresh Rate	48 to 76Hz (60 Hz recommended)
Dimensions (W x H x D)	24.2" x 20.5" x 9.1" (612.84 mm x 519.39 mm x 229.63 mm)
Dimensions without Stand	24.2" x 14.5" x 2.1" (612.84 mm x 367.46 mm x 52.3 mm)
Panel Depth	2.1" (52.3 mm)
Display Weight	10.8 lb/4.9kg (7.0 lb/ 3.145 kg without stand)
Shipping weight	13.3 lb (6.8 kg)
Video Inputs	HDMI, DisplayPort, VGA
HDCP	Yes

<b>Webcam</b>	2.0 MP FHD camera with microphone and LED indicator (for Windows 10 Hello)
<b>Audio Output</b>	Integrated 2W/channel stereo speakers, headphone jack
<b>External Connections</b>	HDMI 19-pin, DisplayPort 20-pin, VGA 15-pin, 3.5 mm audio in, 3.5mm headphone out
<b>Compatibility</b>	PC and Mac® (adapter may be required for Mac)
<b>Power Supply</b>	Internal
<b>Power Consumption (max)</b>	14.7W Typical (<0.5W standby)
<b>Power Requirements</b>	AC 100/240 VAC
<b>Operating Temperature</b>	0° to +40°C (32° to 104°F)
<b>Humidity</b>	10 - 85% RH (non-condensing)
<b>Mount</b>	Built-in 100 mm VESA, back
<b>Product Approvals</b>	cTUVus, CE , FCC-B, RoHS
<b>Recommended Usage</b>	Up to 16 hours per day
<b>Service and Support</b>	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
<b>Options / Features</b>	IPS panel, Wide color consistent viewing angle, Discreet branding, Height adjustment: 4.3" (120cmm), Swivel range 60° (30° left, 30° right), Pivot ± 90°, Anti-glare coating ,Multi-language display, On screen display (OSD), Kensington® Security Slot
<b>Blue Light Reduction</b>	Yes
<b>Flicker Free</b>	Yes
<b>In the Box</b>	PXV2410 24" LED LCD Monitor, Power Cord, HDMI Cable, DisplayPort Cable, USB Cable, User's Guide
<b>UPC</b>	8 10689 00987 0

For more information, please visit [www.planar.com](http://www.planar.com)

*Specifications are subject to change without notice.*

*Specification Report Date: 6/9/2022*

*© Copyright 2022 Planar Systems, Inc. All rights reserved*