



4XEM's 8K DisplayPort Bi-Directional Switch

4XEM Part- 4X8KW002



4XEM's 8K DisplayPort Bi-directional switch offers manually controlled video switching at 8K, 5K or 4K quality resolution. Able to function in two distinct modes, this switch can either connect two devices to a monitor or one device to two monitors (simultaneous video output is not supported). Regardless of function the video quality will remain at the desired high-quality resolution. Set-up is very intuitive plug and play designed for quick video access, coupled with its portable design this switch can be used transferred as needed. Boost your DisplayPort video resolutions easily with 4XEM's 8K switch.

Problem it solves: Offering 8K, 5K, and 4K video quality and switch between displays or devices, 4XEM's 8K DisplayPort Switch is a great addition to any workstation.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep 1-866-999-4936 Ext.104 tschaus@4xem.com







Features

- Two DisplayPort 1.4 ports
- · Comes with DC power cable
- Supports 2 device connection to one monitor
- Supports one device to two monitors (simultaneous video output not supported)
- Supports 8K@30Hz
- Supports 5K@60
- Supports 4K@120Hz, 60Hz
- LED Power indicator
- Compatible with Mac OSX and Windows
- Manually controlled device control

Application

- Home theatre
- Office
- Business Presentations
- · Multi-screen display



4XEM Products Are Available At Your Favorite Online Retailers

Contact Todd Schaus 4XEM sales Rep 1-866-999-4936 Ext.104 tschaus@4xem.com



DATA SHEET

Warranty Information Warranty 1 Year

Hardware **Industry Standards** DisplayPort 1.4

DSC 1.2

Nο Remote

Video Connector Type DisplayPort Connector(s)

Video Input/Outputs

Other Micro-USB (for power only)

Max Uncompressed Bandwidth HBR3 - 32.4Gbps/25.92Gbps Performance

7680x4320 (8K), 30Hz, 8bpc (Uncompressed) Maximum Digital Resolutions

3840x2160 (4K), 120Hz, 8bpc (Uncompressed)

Power Source USB Powered (Adaptor not included) Power

Input Voltage 5V DC @ 2A

Power Consumption 10W

Colour Black Physical Characteristics

Shell Material Aluminum Buttons/Switches I/O Selector LED Indicators 2 (Active I/O) Power Cable (Micro-USB) Length

3.05 ft [0.93 m] Product Height 0.53 in [13.4 mm] Product Width 2.76 in [70.0 mm] Product Length 2.05 in [52.0 mm] Weight of Product 1.55 oz [44 g]

Packaging Information Package Type Poly-bag

> Package Height 7.76 in [197 mm] Package Width 5.83 in [148 mm] Package Length 0.71 in [18 mm] Shipping (Package) Weight 2.61 oz [74 g]

What's in the Box Included in Package 1x DisplayPort Bidirectional Switch

1x Micro-USB Power Cable

"External Power Supply required; DP voltage insufficient for Notes Notes

proper operation.

2 operating modes; single display with selectable video source, and single video source with selectable display. Higher bandwidths (resolution, refresh rate, colour depth) are achievable with DSC (This feature must also be supported by your display and graphics card/video source

equipment).

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep tschaus@4xem.com 1-866-999-4936 Ext.104



^{*} Product appearance and specifications are subject to change without notice

^{*} Same day shipping is only available for orders shipping within the United States