



TR311HWV2

AI Auto Tracking

12X HD PTZ Streaming Camera



Professional Quality Video for Everyone.

The AVer TR311HWV2 AI Auto Tracking Camera in white gives you lots of flexibility with multiple tracking modes, outputs and upgradeable to NDI/HX! The 12X optical zoom and HD resolution offer the range and picture quality for medium to large rooms. The advanced artificial intelligence (AI) technology allows you to track your speaker (full or half body), pre-set shoot zone, or with hybrid mode without a dedicated camera operator. New voice tracking (with PTZ Link software and select microphones) and gesture control features give presenters even more control.

With PoE+, SRT, LAN, USB type B to PC, Virtual USB, RS232, HDMI-Out, AVer control and management software, and compatibility with all popular video platforms, you have all you need to connect with ease in any environment.

Our industry-leading AVerCare warranty program offers 3 years protection and 24-hour replacement to give you total peace of mind.



3 Auto Tracking Modes



12X Optical Zoom



HDMI, IP, USB Output



Full HD 1080p60



PoE+ Support



Wide Dynamic Range

People Tracking

- Capture every interaction
- Either track full body or half body
- Simple click to track and manually follow an additional presenter via remote control or Web UI



Zone Tracking

- Establish preset zones
- Create video focused on content
- Enhance the capture of content on multiple displays



Hybrid Mode

- Camera auto switch between Presenter vs Zone mode
- Combines the best features of Presenter and Zone mode
- Flexibility of tracking presenter freely or fixed content



Voice Tracking

With the aid of PTZ Link and select microphones, you can easily turn AVer PTZ camera to a voice tracking camera through setting preset points. Accomplish all this without having to hire expensive programmers!



Wide Dynamic Range

The Wide Dynamic Range (WDR) of the camera uses special algorithms to balance dark or bright lighting for one clear image.



Tally Light

Simplify multi-camera live video productions with an illuminated red light on the active camera.





Free Software for Users and AV Managers

Whether you need a simple tool to control your PTZ or TR camera, or manage over a hundred on your network, AVer has great options. [CaptureShare](#) and [PTZ Management](#) for desktop and [AVER PTZ Control Panel](#) for iPad have you covered. For new voice tracking features, look to [PTZ Link](#). Visit our [support](#) page for easy download of our desktop software.

Compatible Software



Extron



vMix




NewTek



Microsoft Teams

Product Specifications

Camera	Sensor Size	1/2.8"CMOS	I/O Interface	Video Output	HDMI, IP, USB
	Pixel	2MP		Audio Output	HDMI, IP, USB
	Output Resolution	Resolution: 1080p/720p Frame Rate: 60/59.94/50/30/29.97/25		Audio Input	MIC in/Line in
	TV Line	900 (center/wide)		Baud Rate	2400, 4800, 9600, 38400
	Focal Length	f=3.9 ~ 46.8mm		Control Interface	RS-232/RS-422/Ethernet
	Iris	F=1.6 (Wide) ~ 2.8 (Tele)		Control Protocol	VISCA/PELCO-D (RS232/RS422/IP), CGI (IP)
	Optical Zoom	12X		Network Interface	10/100/1000 Base - T
	Digital Zoom	12X		USB	3.0
	Total Zoom	144X		POE+	PoE+ (IEEE802.3at)
	D FOV	78° (wide) ~ 7° (Tele)		Power Requirements	12V
	H FOV	70° (wide) ~ 6° (Tele)		Connector	USB3.0 (typeB)
	V FOV	42° (wide) ~ 3° (Tele)		Video Format	MJPEG/YUY2
	Minimum Illumination	0.5 lx (50 IRE, F1.6, Max. AGC, 1/30)		Resolution (Max)	1080P
	Minimum Working Distance	Wide 0.5m, Tele 1.5m		Video Class	UVC 1.1
	Focus	Auto/Manual/One Push		Audio Class	UVC 1.0
	White Balance	Auto/Manual	USB	Channel	2ch (stereo)
	Gain	Auto/Manual		Codec	AAC-LC, PCM
	Shutter Speed	1/1 s to 1/10,000 s		Sample Rate	AAC-LC(48Khz)
	BLC (Back Light Compensation)	Yes		System	IR Remote Control
	Exposure	Auto, Manual, Priority AE (Shutter, IRIS), BLC, WDR		Tally	Yes
Parameter	Noise Reduction	2D/3D NR		Kensington Lock	Yes
	Frequency	50Hz & 60Hz		Power Consumption	19W
	S/N Ratio	≥50dB		Operating Temperature	0°C ~ +40°C
	Image Effect	Mirror/Flip Freeze/WDR/BLC		Operating Humidity	20%~80%
	WDR (Wide Dynamic Range)	Yes		Storage Temperature	-20°C ~ +60°C
	Pan Angle	-170° ~ +170°		Storage Humidity	20% ~ 95%
IP Streaming	Tilt Angle	-30° ~ +90°		Dimensions	W180*D145*H192mm
	Pan Control Speed	0.1 ~ 100°/Sec		Net Weight	2 kg (+/-0.1) (4.41 lbs)
	Tilt Control Speed	0.1 ~ 100°/Sec		Application	Indoor
	Preset Speed	Pan: 200°/Sec, Tilt: 200°/Sec		Accessory	Remote control, 12V power adapter, power cable, Din8 to D-Sub9 cable, RS232 in/out cable, screw for mount, ceiling mount, cable fixing plates, quick guide.
	Preset Number	10 Locations by Remote, 256 vis RS232		Software Tools	AVER PTZ Management, CaptureShare, PTZ Control Panel , PTZ Link, OBS Plug In
	Resolution (Max)	1080P (60PFS)	Warranty	Camera	3 Years
	Video Compression	H.264, H.265,MJPEG		Accessories	1 Year
	Audio Compression	AAC, PCM	Tracking	Mode	Presenter, Zone, Hybrid
	Protocol	IPv6, IPv4, TCP, UDP, ARP, ICMP, IGMP, HTTP, DHCP, RTP/RTCP, RTSP, RTMP, VISCA over IP		Mechanism	Human detection (half or full body)
	Bitrate	512Kbps ~ 32Mbps	Ordering Info	Part Number	PATR3HWV2
	Bitrate Control Mode	VBR/CBR			
	SRT Protocol	Yes			



AVER Information Inc. Americas
668 Mission Court, Fremont, CA 94539
Toll free 1.877.528.7824 T 408.263.3828 F 408.263.8132

©2022 AVER Information Inc. All rights reserved.
All brands and logos are trademarks of their respective companies. Specifications subject to change without notice

pro.averusa.com