



V7 23.8" FHD 1920x1080 IPS LED Monitor

L238IPS-N

SKU: 9UZ740

The sleek L238IPS monitor from V7 is a stunning display and features HDMI, VGA and DisplayPort inputs. The 23.8" display has HD 1920x1080 resolution, vivid colors and integrated speakers, for a great multi-media experience. It also features an IPS Panel for a wide viewing angle. Additionally, the display is VESA 100x100mm mountable to free up desk space, making it a smart choice for the home or office.

- 1920 x 1080 Full HD Resolution for an excellent viewing experience
- IPS Panel Technology ensures visibility in almost every viewing angle
- Input options HDMI, DisplayPort and VGA – HDMI cable included
- Mount ready with 100 x 100 VESA pattern
- Ultra-thin bezel design for a high-end appearance

General

Sku: 9UZ740
 Model: L238IPS-N
 EAN: 0662919114867
 Warranty: 3 years
 Compliance: CE, Energy Star, FCC, ICES, RoHS, UKCA, WEEE
 Country Of Origin: China
 Package Type: One Color
 ASIN: B09M8QTKDB
 SAP: 5349843
 Package Includes: Monitor with Stand, VESA Adapter, 2 x M4x12, 2 x M4x30, Quick installation guide, HDMI Cable, US Power Cord, Power Adapter, Warranty Card

Color

Color: Black

Design

Monitor Feature: Fixed Stand

Package Dimensions

Package Dimensions (L/W/H): 59.4 x 12.3 x 38.6 cm (23.4 x 4.8 x 15.2 in)
 Shipping Weight: 3.4 kg (7.5 lbs)
 Package Weight: 3.4 kg (7.5 lbs)

Product Dimensions

Product Dim (L/W/H): 54.2 x 19 x 40.9 cm (21.3 x 7.4 x 16 in)
 Product Weight: 2.76 kg (6.1 lbs) / without stand
 2.37 kg (5.22 lbs)

California Prop 65

No warning required

Technical

MTBF: 30,000 hrs
 Panel Size: 23.8 in
 Panel Type: IPS
 Power Input: AC 100V-240V 50-60Hz
 Aspect Ratio: 16:9
 Response Time: 14 ms
 Viewing Angle: 178°H / 178°V
 Maximum Resolution: 1920 x 1080
 Screen Coating: Matte
 Brightness: 220 nits
 Color Depth: 16.7 million colors
 Contrast Ratio: 1200:1
 Input Port: DisplayPort, HDMI, VGA
 VESA Mount: 100 x 100 mm
 Input AC Plug Type: NEMA 5-15P (US)
 Stand: 18.8 cm (7.4 in) Height / 22.9 cm (9 in) x 18.9 cm (7.4 in) Base
 Speaker: 2 x 2W
 Monitor Dim (w/o Stand): 54.2 x 32.1 x 5.3cm (21.3 x 12.6 x 2.1in)
 Pixel Pitch (H/V): 0.2745 (H) x 0.2745 (V)
 Horizontal Frequency: 60Hz
 Display Area (H x L): 52.7 cm x 29.6 cm