



## TS-864eU-4G

CPU	Intel® Celeron® N5105/N5095 4-core/4-thread processor, burst up to 2.9 GHz
CPU Architecture	64-bit x86
Graphic Processors	Intel® UHD Graphics
Floating Point Unit	Yes
Encryption Engine	Yes (AES-NI)
Hardware-accelerated Transcoding	Yes
System Memory	4 GB SO-DIMM DDR4 (1 x 4 GB)
Maximum Memory	16 GB (2 x 8 GB)
Memory Slot	2 x SO-DIMM DDR4
Flash Memory	4GB (Dual boot OS protection)
Drive Bay	8 x 3.5-inch SATA 6Gb/s, 3Gb/s
Drive Compatibility	3.5-inch bays: 3.5-inch SATA hard disk drives 2.5-inch SATA hard disk drives 2.5-inch SATA solid state drives
Hot-swappable	Yes
M.2 Slot	Optional via a PCIe adapter
SSD Cache Acceleration Support	Yes
2.5 Gigabit Ethernet Port (2.5G/1G/100M)	2 (also support 10M)
Wake on LAN (WOL)	Yes
Jumbo Frame	Yes
PCIe Slot	1 Slot 1: PCIe Gen 3 x2

USB 2.0 port	2
USB 3.2 Gen 2 (10Gbps) Port	2 x Type A USB 3.2 Gen 2
HDMI Output	1, HDMI 1.4b
Form Factor	2U Rackmount
LED Indicators	HDD 1-8, Status, LAN, Expansion, Power
Buttons	Power, Reset
Dimensions (HxWxD)	88.6 × 482.14 × 318.13 mm
Weight (Net)	6.68 kg
Weight (Gross)	9.25 kg
Operating temperature	0 - 40 °C (32°F - 104°F)
Storage Temperature	-20 - 70°C (-4°F - 158°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	300W, 100-240V
Power Consumption: HDD Sleep Mode	24.776 W
Power Consumption: Operating Mode, Typical	51.022 W
Fan	2 x 80mm, 12VDC
System Warning	Buzzer
Max. Number of Concurrent Connections (CIFS) - with Max. Memory	1500

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

Warning: Using unsupported modules may degrade performance, cause errors, or prevent the operating system from starting.

\* Sound Level Test

Environment: Refer to ISO 7779; Maximum HDD loaded; Bystander Position; Average data from 1 meter in front of operating NAS.

Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.