



Summit E14Evo A12M-030CA

OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
Color	Ink Black
Screen Size / Type	14" FHD+ (1920x1200), 60Hz 100% sRGB
Resolution/ Ratio	1920x1200 16:10
CPU/Processor	Core i7-1280P
CPU Frequency	1.8 - 4.8Ghz
Graphics	Intel Iris Xe
System Memroy	LPDDR5 16GB
SoDimm	On board with Dual channel design
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	1 x NVMe M.2 SSD by PCIe Gen4 x4
WLAN	Killer WiFi 6E AX1675 (2x2)
BT	BT 5.2
Card Reader	Micro SD
HDMI-out	4K @ 60Hz
USB Type C	Thunderbolt 4*2 [Support Power delivery, DP 1.4a, USB 4.0]
USB	USB 3.2 Gen2 (Type-A) *1
Keyboard	White backlight keyboard (99 Key)
Touch Pad	Silky Glass Multi Touch with Finger print reader [Support FIDO 2]
Mic-in/ Headphone-out	Mic-in/Headphone-out Combo
Speaker	Speakers 2W * 2
Webcam	IR FHD Type [30fps/1080p]
Battery Pack	4 cell (72Whr) Li-Polymer
AC Adapter	65W
Unit weight	3.61 lbs
Unit Dimension	12.36" x 8.96" x 0.70"
UPC	824142279960
UCC-14	10824142279967
Warranty	1 year Limited warranty (Include 1 Year Global)