

### PERFORMANCE

#### Processor

Intel® Core™ i5-1235U, 10C (2P +8E) / 12T, P-core 1.3 / 4.4GHz, E-core 0.9 / 3.3GHz, 12MB

#### Graphics

Integrated Intel UHD Graphics

#### Chipset

Intel SoC Platform

#### Memory

8GB Soldered DDR4-3200

#### Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

#### Max Memory

Up to 16GB (8GB soldered + 8GB SO-DIMM) DDR4-3200 offering

#### Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

#### Storage Support

Model with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB

#### Card Reader

None

#### Optical

None

#### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

#### Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

#### Camera

720p with Privacy Shutter

#### Microphone

2x, Array

#### Battery

Integrated 38Wh

#### Max Battery Life

Model with 38Wh battery:

MobileMark® 2018: up to 5.3 hr

Local video (1080p) playback@150nits: up to 6.85 hr

#### Power Adapter

65W USB-C (2-pin)

### DESIGN

#### Display

15.6" FHD (1920x1080) TN 250nits Anti-glare, 45% NTSC

#### Touchscreen

None

#### Keyboard

Non-backlit, English

#### Case Color

Business Black

#### Surface Treatment

Texture

#### Case Material

PC + ABS (Top), PC + ABS (Bottom)

#### Dimensions (WxDxH)

359 x 236 x 19.9 mm (14.13 x 9.29 x 0.78 inches)

#### Weight

Starting at 1.7 kg (3.74 lbs)

### SOFTWARE

#### Operating System

Windows® 11 Pro 64, English

#### Bundled Software

Office Trial

### CONNECTIVITY

#### Ethernet

100/1000M

#### WLAN + Bluetooth®

Wi-Fi® 6 11ax, 2x2 + BT5.2

#### Standard Ports

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.2)
- 1x HDMI®, up to 2.5K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

### SECURITY & PRIVACY

#### Security Chip

Firmware TPM 2.0

#### Fingerprint Reader

None

#### Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

#### Other Security

Camera privacy shutter

### SERVICE

#### Base Warranty

1-year, Depot

#### Included Upgrade

None

### ACCESSORIES

#### Bundled Accessories

None

### CERTIFICATIONS

#### Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

#### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

### MODEL

TopSeller : Yes

Announce Date : 2022-05-18

EAN / UPC / JAN : 196800622990

End of Support : 2028-10-22



intel

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.

## Recommended Services

|        |   |
|--------|---|
| BEST   | 3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751) |
| BETTER | 3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0Q81865)                   |
| GOOD   | 3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)         |

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference