DisplayPort™/HDMI™ KVM Switch
For Dual DisplayPort™ 4K 60Hz

Club 3D

Product Name:
DisplayPort™/HDMI™ KVM Switch For Dual DisplayPort™ 4K 60Hz

Product Series: Video Splitter

Product Code: CSV-7210

EAN code: 8719214472238

UPC code: 841615102457

Description:
The CSV-7210 is a high performance DisplayPort™ KVM (Keyboard Video and Mouse) switcher. It routes high definition videos up to 4096x2160 at 60Hz resolution and audio from any DisplayPort™ source to any HDMI™ or DisplayPort™ supported display. This DisplayPort™ KVM switcher not only has the key press switching function, but also has an intelligent function as well as hot pluggable function.

Features:
- Support resolution up to 4Kx2K@60Hz
- Support RGB 4:4:4/ YCbCr 4:4:4/ YCbCr 4:2:2/ YCbCr 4:2:0
- Support KVM function
- Support a DisplayPort™ or HDMI™ display and a set of Keyboard and Mouse to control two PCs with DisplayPort™ ports
- **DisplayPort™**
  Support 8.1Gbps per channel (32.4Gbps all channels) bandwidth
  Support 16bit per channel (48bit all channels) deep color
  Support HDR
- **HDMI™**
  Support 6Gbps per channel (18Gbps all channels) bandwidth
  Support 12bit per channel (36bit all channels) deep color
  Support HDCP 2.2/1.4
  Support HDR
- Support infrared remote control function
- Support for switching LED indications

Supported resolutions:
- Max Resolution: 3840*2160@60Hz, 4096*2160@60Hz

Connectors		
Console Connectors	USB 2.0-A x2(Back)	
	HDMI™ Female x1(Back)	
	DisplayPort™ Female x 1 (Back)	
	3.5mm Stereo Jack (Green, 1 Front, 1 Back) x2	
	3.5mm Stereo Jack (Pink, 1 Front, 1 Back) x2	
KVM Connectors	USB Gen1-B x2 (Back)	
	DisplayPort™ Female x2(Back)	
	3.5mm Stereo Jack(Green, Back) x2	
	3.5mm Stereo Jack(Pink, Back) x2	
USB HUB Connectors	USB Gen1-A x2 (Front)	
Resolution		
Max Resolution	3840*2160@60Hz	
	4096*2160@60Hz	

Operating Frequency	
HDMI™ Bandwidth	18G
DisplayPort™ Bandwidth	32.4G
Mechanical	
Material	Metal
Size (L-W-H)	17.8 x7.5 x 2.6 cm/ 7.0 x 2.95 x 1.02"
Weight (Net)	370 gr / 13.05 4 oz
Environmental	
Operating Temperature	0°C to 45°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10°C to +80°C
Storage Humidity	5% to 90 % RH (no condensation)
Power Requirement	
External Power Supply	DC 5V
Power Consumption	(Max) 12W

OS Support:
- Windows/Linux/Apple Mac OS

In the box:
- CSV-7210 DisplayPort™ KVM Switch x 1
- External Power Supply 5V 3A x 1
- IR Remote Control x1
- IR Extender x1
- USB Type B Male to USB A Male cable x2
- Quick Installation Guide

Available Interfaces

Input:
- **PC 1:** DisplayPort™ + USB + Mic + Stereo Portt
- **PC 2:** DisplayPort™ + USB + Mic + Stereo Port
- 3.5mm Mic Input port
- DC 5V - Power Supply Unit

Output:
- 1x HDMI™ Female
- 1x DisplayPort™ Female
- 1x MIC
- 1x Stereo Jack
- 1x USB Mouse connection
- 1x USB Keyboard connection
- 3.5mm Stereo port

Other info:
- Box size: 23 x 21 x 6.5 cm / 9.05 x 7.08 x 2.56"
- Device size: 17.8 x7.5 x 2.6 cm/ 7.0 x 2.95 x 1.02"
- Box Weight: 147 gr / 5.185 oz
- Device Weight: 370 gr / 13.05 oz
- USB Type B Male cable Weight: 54 gr / 1.91 oz - 2x 108 gr / 3.81 oz
- IR Remote Control incl. battery Weight: 16 gr / 0.57 oz
- IR Extender Weight: 33 gr / 1.16 oz
- Power Adapter Weight: 107 gr / 3.77 oz
- LDPE Bag Weight: 6 gr / 0.21 oz
- Total Weight: 787 gr / x 27.76
- Meets ROHS, FCC, and CE EMI requirements

Please use one of our Extension/Adapter cables to connect to your devices: In case you need assistance to choose the correct cable, please visit our website www.club-3d.com or feel free to mail us at support@club-3d.com and it will be our pleasure to assist you.

Input:

Output:

we Connect
Copyright © 2022, Club 3D B.V. www.club-3d.com