




55" & 65" Neptune™ Partial Sun Outdoor Smart TVs

The Neptune™ Partial Sun Outdoor Smart TV is an all-season solution for outdoor entertainment and living. This outdoor TV is all weather rated, maintenance-free and has an operating temperature range of -22°F - 122°F (-30°C - 50°C). With 4K resolution and an IPS panel, Neptune meets the full UHD specifications, providing exceptional color and video quality from any viewing angle. The Neptune Partial Sun Outdoor Smart TV brings everyone's favorite content and apps outdoors, creating a feature rich outdoor oasis. Whether you want an outdoor TV on your backyard patio or under the gazebo, quality outdoor entertainment is now a reality with Neptune.



All Weather
Rated



Operating
Temperature Range:
-22°F - 122°F
(-30°C - 50°C)

- IPS panel allows for accurate color representation when viewing off axis
- Enjoy content from popular streaming services
- Customizable with hundreds of apps available from the webOS store
- Sealed cable entry helps prevent water and debris from getting inside
- Magic Remote™* is a connected device that allows control of the TV as well as supporting voice commands
- Includes a Neptune™ Outdoor Tilting TV Wall Mount to provide a secure installation

*Note: The Magic Remote™ is not outdoor rated and should not be left outside when the TV is not in use to avoid damage.



powered by webOS Hub

NETFLIX

YouTube

prime video



Spotify



ThinQ AI®

Magic Remote™

4KULTRA HD™

HDR
HIGH DYNAMIC RANGE



RoHS



IP



Bluetooth®



Includes Outdoor Tilting
TV Wall Mount



Includes Outdoor Smart
TV Remote Control



Includes
Magic Remote™

✉ info@neptunetv.com

🌐 neptunetv.com

peerless-AV®
Driving Technology Through Innovation

55" Neptune™ Partial Sun Outdoor Smart TV
65" Neptune™ Partial Sun Outdoor Smart TV

LCD Display

SCREEN SIZE	55" Class (54.64" Diagonal) 65" Class (64.53" Diagonal)
ASPECT RATIO	16:9
RESOLUTION	3840 x 2160
HIGH DYNAMIC RANGE (HDR)	HDR10
BRIGHTNESS	500cd/m ²
COLOR DEPTH	10Bit (1.07 Billion Colors)
COLOR GAMUT	72% NTSC
VIEWING ANGLE	178° Vertical/Horizontal
REFRESH RATE	60Hz
OPERATING TIME	8/7

Environmental

STORAGE AND OPERATING TEMPERATURE	-22°F - 122°F (-30°C - 50°C)
IP RATING	IP54
SAFETY/EMC	FCC Class B, cULus, NOM

Power

AC INPUT	100 VAC to 240 VAC, 50 to 60 Hz
POWER CONSUMPTION	55" Model: Maximum: 138W, Standby:<0.5W
	65" Model: Maximum: 170W, Standby:<0.5W
AUDIO OUTPUT	2x8W

Mechanical

SIZE (W x H x D)	55" Model: 49.09" x 28.54" x 3.11" (1247 x 725 x 79mm) 65" Model: 57.59" x 33.31" x 3.11" (1463 x 846 x 79mm)
WEIGHT	55" Model: 37.5lb (17.01kg) 65" Model: 50.7lb (22.99kg)
VESA MOUNT	55" Model: 300 x 200mm 65" Model: 300 x 200mm
COLOR	Black


Input/Output Connections

TV FORMATS	2160p, 1080p, 1080i, 720p, 480p, 480i
TV INPUT	Coax, 75 ohm (x1) NTSC, ATSC, 256-QAM
HDMI INPUT	HDMI (x3) (HDMI 1.4 / 2.0 with HDCP 1.4 / 2.2) (ARC on HDMI2)
peerCONNECT (CEC)	HDMI 1,2,3
CVBS INPUT	RCA (x1)
LAN	RJ45 (x1)
ANALOG AUDIO INPUT	RCA (x1)
ANALOG AUDIO OUT	3.5mm Stereo Jack (x1)
USB 2.0	USB A (x2)
DIGITAL AUDIO OUTPUT	Optical (x1)
IR REPEATER:	3.5mm Mono Jack (x1)

Package Specifications

	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
55" Model:	53.97" x 33.30" x 8.97" (1371 x 846 x 228mm)	59.5lb (26.99kg)	735029344445	Display, Outdoor Rated Smart TV Remote, Magic Remote™, Manual, Outdoor Tilting TV Wall Mount, IR Emitter, Adhesive Cable Tie Holder (x3), Technical Support Insert, Warranty Insert	1
65" Model:	62.51" x 38.46" x 8.97" (1588 x 977 x 228mm)	78lb (35.38kg)	735029344452		

All dimensions = inch (mm)



Display Size	Dimension "A"	Dimension "B"	Dimension "C"	Dimension "D"	Dimension "E"	Dimension "F"	Dimension "G"	Dimension "H"	Dimension "I"	Dimension "J"	Dimension "K"
55" Model:	54.64" (1388mm)	28.54" (725mm)	49.09" (1247mm)	1.61" (41mm)	3.11" (79mm)	11.81" (300mm)	18.65" (474mm)	7.87" (200mm)	4.61" (117mm)	26.85" (682mm)	47.69" (1211mm)
65" Model:	64.53" (1639mm)	33.31" (846mm)	57.59" (1463mm)	1.61" (41mm)	3.11" (79mm)	11.81" (300mm)	22.89" (582mm)	7.87" (200mm)	5.42" (138mm)	31.62" (803mm)	56.24" (1428mm)

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor TVs, kiosks, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV
2300 White Oak Circle
Aurora, IL 60502 USA
(800) 865-2112
(630) 375-5100
Fax: (800) 359-6500

Peerless-AV Latin America
Av. de las Industrias 413
Parque Industrial Escobedo
General Escobedo, N.L.,
México, 66062
+52 (81) 8384-8300
Fax: +52 (81) 8384-8360

peerless-av®
Driving Technology Through Innovation