



# ASUS P1512

## Easy portability. Effortless productivity.

Whether for work or play, ASUS P1512 is the entry-level laptop that delivers powerful performance and immersive visuals. Its NanoEdge display boasts wide 178° viewing angles and a matte anti-glare coating for a truly engaging experience. A dual-storage design with up to a 1 TB PCIe® SSD and a 1 TB HDD gives you the perfect combination of large storage capacity and fast data read/write speeds.



Up to 11<sup>th</sup> Gen CPU

WiFi 5

### Empower your efficiency

- Up to the 11th Gen Intel Core i7 processor
- Up to 16GB DDR4 RAM
- Supercharged data transfer with up to 1TB HDD & 1TB SSD

Dual Storage

NanoEdge Display

### Get a wider view of the world

- Frameless two-sided NanoEdge display with 83% screen-to-body ratio
- 1920 x 1080 FHD display
- 178° wide viewing display
- ASUS Splendid software tuning accurate colors
- ASUS Eye Care Technology to reduce blue light levels by up to 30% for a comfortable reading experience
- ASUS TrueLife video increase 150% contrast

Kensington lock security

EAR HDD protection

### Business-grade security & reliability

- Kensington lock slot to prevent theft of the PC. Enhanced protection
- EAR™ HDD shock dampening protection
- Metal brace underneath the keyboard
- Fingerprint sensor (optional)
- BIOS Booting User Password Protection

\*Specifications may vary by country and region.

### Warranty and Support

- 3-Year global warranty<sup>2</sup> 100% free of charge, with no hidden costs.
- Pick Up & Return service Enjoy a door-to-door service including pick up, repair, and return.
- MyASUS App Contact customer service, view repair status, read product guides and more.

### Contact Us

Commercial Support – Contact Us  
Self-service:  
Phone:  
Email:

Commercial Sales – Volume Purchase  
Inquiries  
Email:  
For more information:

# SPECIFICATION



Model	P1512
Operating System	Windows 11 Pro (ASUS recommends Windows 11 Pro) Windows 11 Home
CPU	Intel® Core™ i7-1165G7 Processor 2.8 GHz (12M Cache, up to 4.7 GHz, 4 cores) Intel® Core™ i5-1135G7 Processor 2.4 GHz (8M Cache, up to 4.2 GHz, 4 cores) Intel® Core™ i3-1115G4 Processor 3.0 GHz (6M Cache, up to 4.1 GHz, 2 cores)
GPU	Intel® Iris Plus
Memory	1 x SO-DIMM, up to 16 GB DDR4 3200MHz Onboard: 4 GB/8 GB DDR4 3200 MHz
Storage	Up to 1TB SATA 5400RPM 2.5" HDD 128G / 256G / 512G / 1TB M.2 NVMe PCIe® 3.0 SSD
Display	15.6" LED Back-lit-Narrow border 200nits HD TN 1366X768 16:9 Anti-Glare NTSC45% 15.6" LED Back-lit-Narrow border 220nits FHD TN 1920X1080 16:9 Anti-Glare NTSC45% 15.6" LED Back-lit-Narrow border 250nits FHD value IPS TN 1920X1080 16:9 Anti-Glare NTSC45%
I/O Port	1 x USB 3.2 Gen 1 Type-A / 1 x USB 3.2 Gen 1 Type-C / 2 x USB 2.0 Type-A 1 x HDMI 1.4 / 1 x 3.5mm Combo Audio Jack / 1 x DC-in
Video Camera	720p HD camera
Wireless	Wi-Fi 5 (802.11 ac) Bluetooth® 5.0 Wi-Fi 5 (802.11 ac) Bluetooth® 4.1 Wi-Fi 6 (802.11 ax) Bluetooth® 5.2
Audio	2 x speaker, 2 x multi-array microphone, ASUS SonicMaster stereo audio system, Cortana voice-recognition support
Weight	1.8Kg
Dimensions (WxDxH)	36 x 23.59 x 1.99 cm
Battery	37Wh 2-cell battery
Security	Firmware TPM (fTPM) / Windows Hello login with Fingerprint (optional) BIOS Booting User Password Protection / McAfee LiveSafe™ 30-day trial
Keyboard	Illuminated Chiclet Keyboard (optional)
AC adapter	65W AC Adapter: Output: 19V DC, 3.42A / Input: 100 – 240 V AC, 50/60Hz universal
Energy efficiency compliance	Energy star, EPEAT

1. The Windows 11 upgrade will be delivered to qualifying devices for 2021 and 2022. For more info, visit [https://www.asus.com/business/enterprise/specs/faq/windows11\\_upgrade](https://www.asus.com/business/enterprise/specs/faq/windows11_upgrade).  
2. ASUS Express Service Package may differ by country. For details, visit [https://www.asus.com/business/enterprise/specs/faq/windows11\\_upgrade](https://www.asus.com/business/enterprise/specs/faq/windows11_upgrade).

### Recommended Accessories

