



BUSINESS & PRODUCTIVITY ALL-IN-ONE PC

PRO AP242 12M

PRO AP242 12M-071US

Specification

Manufacturer Part #	PRAP24212M071
Color	BLK
Operating System	Windows 11 Home
Processor	Intel® Core™ i5-12400 6P+0EC/12T 18MB Cache
Chipset	H610
Display	23.8" FHD IPS-Grade 1920x1080, LED, Matte
Display Type	Non-touch
Graphics	Intel® Iris Xe
Memory	16GB DDR4 (2 x 8GB)
Memory Slots	2x DDR4 2666/3200MHz SO-DIMM, up to 64GB
Storage	512GB M.2 NVMe SSD
Optical Drive Type	N/A
LAN	1 x RJ45 (1GbE) Realtek RTL8111H
WLAN	WiFi 6 (802.11ax) 2.4Gbps, Dual Band 2.4GHz, 5GHz
Bluetooth	BT 5.2
Included Peripherals	Wireless Keyboard & Mouse
Audio	2 x 3W HD Speakers
VGA	N/A
Video I/O	1 x DP-out, 1 x HDMI-out
USB 2.0	2 x USB 2.0 (side)
USB 3.1/3.2	1 x USB 3.2 Gen2 Type-C (rear) 1 x USB 3.2 Gen2 Type-A(rear) 2 x USB 3.2 Gen1 Type-A (rear)
COM Port	N/A
Mic in / Headphone out	1 x Mic-In/1 x Headphone-Out
Webcam	Built in 1080p (FHD) w/Dual-array Mic
Stand	Fixed
Power Adapter	120W
Dimensions	24.41" x 8.78" x 19.13"
Weight	10.21 lbs
Warranty	1 Year