

# ViewSonic® LCD DISPLAY **VX1755**

## Key Features

- Ultralight 1kg design with sleek metal casing
- Adjustable kickstand from 0 to 62 degree
- AMD FreeSync Premium
- 144Hz Refresh Rate
- Diverse connectivity with USB Type-C and mini-HDMI



## Product Description

The ViewSonic VX1755 Full HD IPS-panel portable monitor is the latest in portable gaming displays. With AMD FreeSync Premium and a 144 Hz refresh rate, gamers on the go can get the best experience wherever they play. A versatile kickstand makes it easy to set up anywhere for single-player and multiplayer sessions. The ultralight 1 kg design is supremely portable while a robust metal casing will make sure the screen survives the trip. Having both USB-C and mini-HDMI ports enable use with gaming devices ranging from consoles to laptops, connecting to both data and power easily.

**Visit Us** [www.viewsonic.com](http://www.viewsonic.com)

## DISPLAY

Display Size (in.):	17
Viewable Area (in.):	17.3
Panel Type:	IPS Technology
Resolution:	1920 x 1080
Resolution Type:	FHD (Full HD)
Static Contrast Ratio:	800:1 (typ)
Dynamic Contrast Ratio:	80M:1
Light Source:	LED
Brightness:	250 cd/m <sup>2</sup> (typ)
Colors:	16.7M
Color Space Support:	8 bit (6 bit + FRC)
Aspect Ratio:	16:9
Response Time (Typical GTG):	4ms
Viewing Angles:	170° horizontal, 170° vertical
Backlight Life (Hours):	15000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	144
Variable Refresh Rate Technology:	FreeSync Premium
Blue Light Filter:	Yes
Color Gamut:	NTSC: 45% size (Typ) sRGB: 64% size (Typ)
Pixel Size:	0.199 mm (H) x 0.199 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

## COMPATIBILITY

PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080
PC Operating System:	Windows 11 certified; macOS tested
Mac® Resolution (min):	1920x1080

## CONNECTOR

USB 3.2 Type C DisplayPort Alt mode only :	1 (60W power charger)
3.5mm Audio Out:	1
Mini HDMI:	1
Power in:	USB Type C (power only)

## AUDIO

Internal Speakers:	0.8Watts x2
--------------------	-------------

## POWER

Eco Mode (Conserve):	10W
Eco Mode (optimized):	11W
Consumption (typical):	12W
Consumption (max):	13W
Voltage:	AC 100-240V

## CONTROLS

Physical Controls:	Key 1 (favorite), Key 2, Key 3, Key 4, Key 5 (power)
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

## OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

## INPUT SIGNAL

Frequency Horizontal:	mini HDMI (v2.0): 24 ~ 165KHz, Type C: 165 ~ 165KHz
Frequency Vertical:	mini HDMI (v2.0): 48 ~ 144Hz, Type C: 48 ~ 144Hz

## VIDEO INPUT

Digital Sync:	TMDS - mini HDMI (v2.0), Micro-Packet - Type C
---------------	--

## ERGONOMICS

Tilt (Forward/Back):	20° / 62°
----------------------	-----------

## WEIGHT (IMPERIAL)

Net (lbs):	2.2
Net Without Stand (lbs):	2.2
Gross (lbs):	4.9

## WEIGHT (METRIC)

Net (kg):	1
Net Without Stand (kg):	1
Gross (kg):	2.2

## DIMENSIONS (IMPERIAL) (WXHXD)

Packaging (in.):	19.5 x 15.6 x 3
Physical (in.):	15.6 x 9.7 x 0.7
Physical Without Stand (in.):	15.6 x 9.7 x 0.7

## DIMENSIONS (METRIC) (WXHXD)

Packaging (mm):	495 x 395 x 77
Physical (mm):	396 x 247 x 17
Physical Without Stand (mm):	396 x 247 x 17

## GENERAL

Regulations:	cTUVus, FCC-B, ICES003, Energy Star, CEC, NRCAN, NOM, Mexico Energy, CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO
--------------	--

PACKAGE CONTENTS:	VX1755 x1, mini HDMI to HDMI Cable (v1.4; Male-Male) x1, USB Type-C Cable (Male-Male) x1, USB Type-C to Type-A 3.2 Gen1 Cable (Male-Male) x1, AC/DC Adapter x1,
-------------------	---

Stand-by:	0.5W	Quick Start Guide x1, Protect cover x1
Power Supply:	External Power Adaptor	
Recycle/Disposal:		Please dispose of in accordance with local, state or federal laws.
Warranty:		*Warranty offered may differ from market to market
Power Management:		Energy Star standards

Copyright © ViewSonic Corporation 2000-2024. All rights reserved.