



BUSINESS DEVICES THAT ARE A CLASS APART



The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

ThinkPad T14s Gen 3 (AMD)

Smarter
technology
for all

Lenovo

Professionals who are always on-the-move need a laptop powered with up to AMD Ryzen 7 Pro Processor with high processing power. Support of WiFi6E enables faster connection speeds so that users can stay productive in the field without any network congestion. Additionally, optional touch style fingerprint reader on the power button allows instant log in into the system thus preventing data from being compromised.



REASONS TO BUY

Mobile workers will appreciate the Dolby Audio dual stereo speakers and optional dual array microphone that helps with better audio quality and clear reception to calls. While optional privacy shutter prevents intrusion when the camera is not in use.

Up to 32GB LPDDR5 memory and up to 2TB SSD storage drives performance, it enables users to store and access heavy files on the system with ease.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

ThinkPad T14s Gen 3 (AMD)

KEY SPECIFICATIONS

Processor	AMD Ryzen™ 5 / 7 Processor
Operating System	Powered by Windows 11 Pro
Display	14.0" WUXGA (1920x1200), IPS, 300 nits, Antiglare, 600:1 contrast ratio, 45% NTSC 14.0" WUXGA (1920x1200), IPS, 400 nits, Antiglare, 800:1 contrast ratio, 100% sRGB, Low power, Eyesafe® Certified 14.0" 2.2K (2240x1400), IPS, 300 nits, Antiglare, 1000:1 contrast ratio, 100%sRGB, TÜV Low Blue Light Method 2 14.0" 2.8K (2880x1800), OLED, 500nits, Antiglare, 100000:1 contrast ratio,100% DCI-P3, Eyesafe Certified 14.0" WUXGA (1920x1200), Multi-Touch, IPS, 300 nits, Antiglare, 600:1 contrast ratio, 45% NTSC 14.0" WUXGA (1920x1200), Multi-touch, IPS, 500 nits, Antiglare, 800:1 contrast ratio, 100%sRGB, ThinkPad® Privacy Guard
Touchscreen	Touchscreen on WUXGA 300nits or 500nits screen
Graphics	AMD Radeon Graphics 660M/680M
Memory	Up to 32GB LPDDR5-6400
Storage	One drive, up to 2TB M.2 2280 SSD
Optical	
Audio	Stereo speakers, 2W x2, Dolby® Audio™ Dual array microphone, 360° far-field, Dolby Voice (optional)
Battery†	Up to 19.52 hr, 57Wh
Power Adapter	One of the following 45W USB-C (2-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin)
Camera	One of the following FHD 1080p with Privacy Shutter HD 720p with Privacy Shutter IR & FHD 1080p with Privacy Shutter
Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls
Dimensions	317.5 x 226.9 x 16.9 mm (12.5 x 8.93 x 0.67 inches)
Weight	1.23 kg (2.71 lbs)

GREEN CERTIFICATIONS

EPEAT™ Gold, ENERGY STAR® 8.0, ErP Lot 3, TCO Certified 9.0, RoHS compliant

OTHER CERTIFICATIONS

MIL-STD-810H military test passed, (Optional) Eyesafe Certified, (Optional) TÜV Rheinland® Low Blue Light

CONNECTIVITY

I/O Ports	1x USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a), 1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort 1.4a), 1x HDMI, up to 4K/60Hz, 1x Headphone / microphone combo jack (3.5mm). Optional: 1x Smart card reader, 1x Nano-SIM card slot (WWAN support models)
WLAN + Bluetooth	One of the following AMD RZ616 Wi-Fi 6E, 11ax, 2x2 + BT5.2 Qualcomm NFA725A Wi-Fi 6E, 11ax, 2x2 + BT5.2
WWAN	Optional
NFC	Optional
Docking	Various docking solutions supported via USB-C.

SECURITY & PRIVACY

Fingerprint Reader
Smart Card Reader
IR Camera with Windows Hello
Discrete TPM 2.0, TCG certified, with Microsoft Pluton TPM 2.0 integrated in SoC
Touch style fingerprint reader on power button, match-on-chip (optional)
Smart card reader (optional)
Kensington Nano Security Slot
(Optional) Camera privacy shutter
(Optional) IR camera for Windows Hello
(Optional) Human Presence Detection
Mirametrix Glance

MANAGEABILITY

DASH
Non-DASH

Recommended for this device



Lenovo Thunderbolt 3 Essential Dock

Dual 4K displays, blazing-fast 10 Gbps data rates, and a range of optimized ports.

The innovative Thunderbolt™ cable connector delivers data, display, and power to both USB-C and Thunderbolt™ notebooks.

Enjoy dual-display support, up to 4K resolution on each, and blazing-fast 10 Gbps data transfer rates.



Lenovo USB-C Mini Dock

Add powerful capabilities to a PC with a single USB-C connection

Supports enterprise network manageability such as PXE boot, Wake-On LAN

Easily connect to an external 4K or 1080p display with HDMI 2.0 or VGA



On-site Service

If a problem can't be fixed remotely, we will visit your location

Normally next business day service

Agreed appointment times

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.