

OS	Windows 11 Home
Color	Titanium Blue
Screen Size / Type	15.6" QHD, Anti-Glare Wide View Angle 240Hz 2.5ms DCI-P3 100%
Resolution/ Ratio	2560x1440 16:9
CPU/Processor	Core i9-12900HK 6+8Core
CPU Frequency	1.8-5 GHz
Graphics	NVIDIA GeForce® RTX3070TI Laptop GPU
Video Memory	8G GDDR6
System Memroy	DDR5 8GB*2 4800MHz
SoDimm	2 Sockets; Max Memory 64GB
HDD Capacity	1TB NVMe PCIe SSD
HDD Interface	NVMe
SSD	2x M.2 SSD Slot PCIe Gen4x4
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2 )
BT	BT 5.2
Card Reader	SD7.0
HDMI-out	v2.1,
Mini-Display Port	v1.4
USB Type C	1x Thunderbolt 4 1x USB 3.2 Gen 2/DP
USB	1 x Type-A USB3.2 Gen2, 2 x Type-A USB3.2 Gen1
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Touch Pad	Multi Touch
Mic-in/ Headphone-out	1 Audio Combo (1/8")
Speaker	Sound by Dynaudio, 2x2W Speaker
Webcam	1080p FHD Webcam
Battery Pack	4 cell (99.9Whr) Li-Ion
AC Adapter	280W
Unit weight	5.24 lbs
Unit Dimension	14.09"x 10.51"x 0.92"
UPC	824142293232
UCC-14	10824142293239
Warranty	1 year Limited warranty (Include 1 Year Global)