



GF63 Thin 11SC-693

Manufacturer Part #	GF6311693
OS	Windows 11 Home (MSI recommends Windows 11 Pro for business.)
CPU	Core i5-11400H
CPU Speed	2.7 - 4.5GHz
Chipset	HM470
Color	Black
Screen Size	15.6" FHD (1920*1080), IPS-Level 60Hz 45%NTSC Thin Bezel
Resolution	1920x1080 (16:9)
GPU	NVIDIA GeForce® GTX 1650 Max-Q
Video Memory	4G GDDR5
Keyboard	Red keyboard with Anti-Ghost key (99 Key)
Audio	Nahimic Audio
Speaker	Speakers 2W*2
Memory	8GB (8G*1) DDR4 3200MHz
HDD Capacity	256GB NVMe SSD
HDD Interface	NVMe
Optical Drive Type	–
LAN	Gb LAN
WLAN	Intel Wi-Fi 6 AX201(2*2 ax)
Bluetooth	BT 5.1
Card Reader	–
Webcam	720p HD Webcam
USB	3x USB 3.2 Gen1
Type-C Port	1x USB 3.2 Gen1 Type C
Video Port	HDMI (supports 4K@60hz)
Audio Port	1 Mic in/ 1 headphone out
AC Power Adaptor	120W
Battery Pack	3 cell (51Whr)
Dimension	14.13"x9.99"x0.85"
Weight	4.10 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)