

PERFORMANCE

Processor

MediaTek Helio G90T (8C, 2x A76 @2.05GHz + 6x A55 @2.0GHz)

Graphics

Integrated ARM Mali-G76 MC4 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4x (uMCP, DRAM)

Storage

64GB (uMCP, UFS 2.1)

Expandable Memory

MicroSD Card (Up to 256GB, FAT32; 1TB, exFAT)

Card Reader

MicroSD Card Slot

Storage Support

- 64GB uMCP (UFS-Based MCP, UFS 2.1)
- MicroSD card, supports FAT32 file up to 256GB, exFAT file up to 1TB

Camera

Front 8.0MP + ToF Sensor / Rear 13.0MP

Microphone

2x, Array

Speakers

4 stereo speakers, 1W x4, optimized with Dolby® Atmos®

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor
- ToF sensor

Vibration Motor

Eccentric Rotating Mass (ERM)

Battery

Integrated 7500mAh (Min.) / 7700mAh (Typ.)

Max Battery Life

Standby time: 4.7 wks

Online video playback time: 12 hr

Talk time: 15 hr (WWAN model)

Browsing time: 12 hr

Music playtime: 15 hr

Charging Time

Fully charges in under 3 hr

Power Adapter

10V / 2.0A

DESIGN

Display

11" 2K (2000x1200) IPS TDDI 400nits, Touch

Touchscreen

10-point Multi-touch

Case Material

PC + 20% GF, Metal

Keyboard

None

Pen

Pen Upgradable

Water Proofing

IP52

Dimensions (WxDxH)

258.4 x 163 x 7.5 mm (10.17 x 6.41 x 0.29 inches)

Weight

Around 490 g (1.08 lbs)

Case Color

Slate Grey

SOFTWARE

Operating System

Android™ 11 or later

CONNECTIVITY

WLAN + Bluetooth®

11a/b/g/n/ac, 1x1 + BT5.1

WWAN

None

VoiceCall

No

Standard Ports

- 1x USB-C® 2.0 (support data transfer, OTG, and Power Delivery 3.0, PE 2.0)
- 1x Pogo pin connector (4-point)

Optional Ports (configured)

1x microSD card slot (WLAN model)

Docking

None

SERVICE

Base Warranty

1-year, Mail-in with 1-year Battery

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product : Lenovo® TB-J616F

TopSeller : No

Announce Date : 2021-06-15

EAN / UPC / JAN : 195890697109



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.


Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Precision Pen 2(US)

ZG38C03380

With 4,096 levels of pressure and tilt detection, the Lenovo Precision Pen 2 affords users the highest level of precision and control as they sketch or just take notes. With up to 100 hours usage*, write or draw all d...



Lenovo Folio Case for Tab P11

ZG38C03348

This folio case is designed to protect your tablet with modern material finish and brimless style. The folio case comes with the stand mode, allowing you to watch rich videos in convenient and comfortable positions. ...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference