



BUSINESS DEVICES THAT ARE A CLASS APART



The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

ThinkPad T14s Gen 3 (Intel)

Smarter
technology
for all

Lenovo

A gold standard of corporate PCs, this redesigned Thinkpad powered by up to 12th Gen Intel processor and Intel Iris Xe graphics has everything the mobile workforce demands in their work devices. An epic all-day battery and MIL standard durability make it an ideal carry-it-anywhere work companion without needing to worry about accidental drops or battery drain. It also ensures maximum security with an optional fingerprint reader integrated with the power button and biometric and AI-based security.



REASONS TO BUY

The 14" display comes in different configurations, such as an OLED screen with a 100000:1 contrast ratio and anti-glare technology for refined details and lifelike visuals – ideal for designing graphics-intensive content or 3D rendering. Choose the optional touch display for seamless computing during travel.

Connect up to 3 external monitors or other equipment through a range of onboard and optional ports, including the dual super-fast Thunderbolt 4 ports for transferring large data-heavy files in a flash.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

ThinkPad T14s Gen 3 (Intel)

KEY SPECIFICATIONS

Processor	12th Generation Intel® Core™ i5 / i7 Processor
Operating System	Powered by Windows 11 Pro
Display	14.0" WUXGA(1920x1200), Multi-touch, IPS, 500 nits, anti-glare, 800:1 contrast ratio, 100% sRGB ThinkPad® PrivacyGuard 14.0" WUXGA(1920x1200), IPS, 400 nits, anti-glare, 800:1 contrast ratio, 100% sRGB Low power, Eyesafe® Certified 14.0" WUXGA(1920x1200), Multi-touch, IPS, 300 nits, anti-glare, 600:1 contrast ratio, 45% NTSC 14.0" WUXGA(1920x1200), IPS, 300 nits, anti-glare, 600:1 contrast ratio, 45% NTSC 14.0" 2.2K(2240x1400), IPS, 300 nits, anti-glare, 1000:1 contrast ratio, 100% sRGB, TÜV Low Blue Light Method 2 14.0" 2.8K(2880x1800), OLED, SDR400nits/HDR500nits, Antireflection/Anti-smudge, 100000:1 ratio, 100% DCI-P3, DisplayHDR™ 500 True Black, Eyesafe Certified
Touchscreen	Optional Touchscreen
Graphics	Intel Iris Xe Graphics in processor
Memory	Up to 32GB LPDDR5-4800
Storage	One drive, up to 2TB M.2 2280 SSD
Optical	
Audio	2x 2W speakers with Dolby Audio speaker system Dual array far-field mics on select models
Battery†	Up to 12.5hrs, 57Wh
Power Adapter	One of the following 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)
Camera	One of the following FHD 1080p with Privacy Shutter HD 720p with Privacy Shutter IR & FHD 1080p with Privacy Shutter
Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls
Dimensions	317.5 x 226.9 x 16.9 mm (12.5 x 8.93 x 0.67 inches)
Weight	starting from 1.21 kg (2.67 lbs)

GREEN CERTIFICATIONS

EPEAT Gold, Energy Star 8.0

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. † Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.

OTHER CERTIFICATIONS

(Optional) Eyesafe Certified, (Optional) Intel Evo™ Platform, (Optional) TÜV Rheinland® Low Blue Light Method 2

CONNECTIVITY

I/O Ports	2x Thunderbolt 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 2.0), 1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 1x HDMI 2.0b, 1x Headphone / microphone combo jack (3.5mm). Optional Ports on select models: 1x Smart card reader, 1x Nano-SIM card slot (WWAN model)
WLAN + Bluetooth	Intel AX211 Wi-Fi 6E, 2x2 + BT5.2
WWAN	Optional
NFC	Optional
Docking	Various docking solutions supported via Thunderbolt.

SECURITY & PRIVACY

Fingerprint Reader
Smart Card Reader
IR Camera with Windows Hello
ThinkPad PrivacyAlert
ThinkPad PrivacyGuard screen
Touch style fingerprint reader on power button, match-on-chip (optional)
Camera privacy shutter (optional)
Smart card reader (optional)
Kensington Nano Security Slot
for Windows Hello
(Optional) Privacy Guard with Privacy Alert
(Optional) Human Presence Detection
Tile ready
(Optional) IR camera

MANAGEABILITY

Intel vPro Enterprise
Non-vPro

Recommended for this device



Lenovo Professional Wireless Keyboard & Mouse

Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection

Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs

Contoured design of the mouse suits both left-handed & right-handed users



ThinkPad USB-C Dock Gen 2

Connects via a single USB-C cable which also charges the PC

1x USB-C, 2x USB2.0, 3x USB3.1 ports (including 1x always-on for charging devices)

2x DisplayPort and 1x HDMI. Supports 1x 4K or 3x Full HD displays



Warranty Extensions

Purchase additional warranty periods from 1 to 5 years

Buy at any point with or after your device purchase

Optional On-site Service