



HP DesignJet Studio 24-in Printer with 3-year Warranty (5HB12H)



Overview

Design meets performance in the world's easiest large-format plotters^[1]

Featuring a modern office design that complements its environment and performance to match. Print multi-size jobs easily with auto switching between roll and tray. Enjoy high-speed printing as fast as 26 sec per A1/D plot. 1 GB memory.

Fits the way you live

Design that performs, technology that stands out.

Fits the way you work

Avoid waiting by the printer with high-speed printing as fast as 26 seconds per A1/D plot.

Extreme simplicity

Print multi-size A3/B and A1/D projects automatically, without manually switching the media source.

[1] The HP DesignJet Studio Printer series and the HP DesignJet T600 Printer series are the only solutions providing seamless printing of both large- and small-format sheets automatically in a multi-size print basket compared to competitive alternatives with comparable size and features as of January, 2020.

Specifications

Print quality color (best)	Up to 2400 x 1200 optimized dpi
Functions	Print
Connectivity, standard	Gigabit Ethernet (1000Base-T), Hi-Speed USB 2.0, Wi-Fi 802.11a/b/g/n, Wi-Fi Direct
Software included	HP Click, HP Smart app, HP Print Preview for Windows, HP Easy Start, HP DesignJet Utility for Windows, HP Support Assistant
Sustainable impact specifications	Free, convenient HP ink cartridge and printhead recycling with HP Planet Partners; FSC®-certified papers and a range of recyclable HP media with a take-back program; First net carbon neutral HP DesignJet plotter; ENERGY STAR® certified
Energy star certified	Yes
Minimum dimensions (W x D x H)	1013 x 555 x 932 mm
Minimum dimensions (W x D x H)	39.9 x 21.9 x 36.7 in
Weight	33.6 kg
Weight	74.1 lb
Power consumption	<35 W (printing), <5.6 W (ready), <2.1 W (sleep), <0.2 W (standby)
Environmental certification	ENERGY STAR; WEEE; EU RoHS; EAEU RoHS; REACH; ErP
What's in the box	HP DesignJet Studio 24-in Printer, printer stand, automatic sheet feeder, roll cover, printhead, introductory ink cartridges, spindle, quick reference guide, setup poster, power cord
Manufacturer Warranty	Three-year limited hardware warranty

Additional specifications

Accessories	B3Q36A HP DesignJet 24-in Spindle;B3Q37A HP DesignJet 36-in Spindle
Acoustic power emissions (active, printing)	5.8 B(A) (operating), <3.4 B(A) (idle)
Acoustic pressure emissions	42 dB(A) (operating), <16 dB(A) (idle)
Color(s) of printing supplies	Cyan, magenta, yellow, black
Dynamic security	Dynamic security enabled printer
Electromagnetic compatibility	Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (EMC/RED Directives), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI); Certified as Class B product: Korea (KCC)
Finished output handling	Sheet feed, roll feed, automatic sheet feeder, media bin, automatic horizontal cutter
High capacity of page yield (colour)	20 ml of ink yields 101 A1/D pages, taking into account maintenance routines[2]
Ink drop	5.5 pl (C, M, Y); 12 pl (K)
Ink types	Dye-based (C, M, Y); pigment-based (K)
Internal Storage	None
Line accuracy	±0.1%[3]
Maximum optical density (black)	8 L* min/2.10 D[4]
Media sizes standard (metric rolls)	279 to 610 mm
Media sizes standard (sheets, rolls)	11 to 24 in
Media sizes supported	Auto sheet feeder: A4, A3; manual feed: A4, A3, A2, A1
Media sizes supported	Auto sheet feeder: A, B; manual feed: A, B, C, D
Media sizes, custom	Auto sheet feeder: 210 x 279 to 330 x 482 mm; manual feed: 210 x 279 to 610 x 1897 mm
Media sizes, custom	Auto sheet feeder: 8.3 x 11 to 13 x 19 in; manual feed: 8.3 x 11 to 24 x 74.7 in
Media thickness	Up to 11.8 mil
Media thickness (metric)	Up to 0.3 mm
Media types	Bond and coated paper (bond, coated, heavyweight coated, plain, bright white, blueprint), technical paper (natural tracing), film (clear, matte), photographic paper (satin, gloss, semigloss, polypropylene), self-adhesive (adhesive, polypropylene)
Media weight, recommended	60 to 280 g/m ² (roll/manual feed); 60 to 220 g/m ² (auto sheet feeder)
Media width, maximum	24 in
Media width, maximum	610 mm
Memory	1 GB

Model size	24 in
Model size	610 mm
Non-Operating Humidity Range	0 to 95% RH
Non-printable area (cut-sheet)	0.2 x 0.2 x 0.2 x 0.7 in (manual feed); 0.2 x 0.2 x 0.2 x 0.2 in (input tray)
Non-printable area (cut-sheet)	5 x 5 x 5 x 17 mm (manual feed); 5 x 5 x 5 x 5 mm (input tray)
Non-printable area (roll media)	5 x 5 x 5 x 5 mm
Non-printable area (roll media)	0.2 x 0.2 x 0.2 x 0.2 in
Number of print cartridges	4 (C, M, Y, K)
Operating altitude	Up to 3000 m
Operating altitude	Up to 9843 ft
Operating humidity range	20 to 80% RH
Operating temperature range	5 to 40°C
Operating temperature range	41 to 104°F
Package dimensions (W x D x H)	1199 x 590 x 524 mm
Package dimensions (W x D x H)	47.2 x 23.2 x 20.6 in
Package weight	43 kg
Package weight	94.8 lb
Playbook TS icon connectivity	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08201987.png
Playbook TS icon dimensions AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08192862.png
Playbook TS icon display AiO	https://h10003.www1.hp.com/digmedialib/prodimg/lowres/c08169148.png
Post consumer recycled plastic in hardware by weight of plastic	10%
Power	Input voltage (auto ranging): 100-240 V (±10%), 50/60 Hz (±3 Hz), 1200 mA max
Print Technology	Ink
Print cartridge volume delivered	80 ml (K); 38 ml (K); 29 ml (C, M, Y)
Print head nozzles	1376
Print heads	1 (cyan, magenta, yellow, black)
Print languages	HP-GL/2, HP-RTL, CALS G4, JPEG, URF
Print multi-size files in one click	Yes
Print speed	26 sec/page on A1, 81 A1 prints per hour[1]
Print speed	26 sec/page on D, 81 D prints per hour[1]
Print technology	HP Thermal Inkjet
Printer drivers included	Raster driver for Windows and macOS
Printing path	Print Anywhere with HP Smart app, HP Click, HP driver for macOS, HP driver for Windows, printing support for Chrome OS, email printing, HP Print Service Plugin for Android, Apple AirPrint

Product logos	AirPrint; Carbon Neutral; ENERGY STAR; Gold IPv6 Ready; Hi-Speed USB; Wi-Fi CERTIFIED; Windows 10 Compatible
Recommended media	HP Universal Bond Paper (FSC® certified)[5] (recyclable)[6];HP Coated Paper (FSC® certified)[5] (recyclable)[6];HP Heavyweight Coated Paper (FSC® certified)[5] (recyclable)[6]
Remote print enabled	Yes
Roll external diameter	100 mm
Roll external diameter	3.9 in
Roll maximum input	1
Roll maximum weight	4.1 kg
Roll maximum weight	9 lb
Safety	USA and Canada (CSA certified); EU (LVD, EN 60950-1 and EN 62368-1 compliant); Russia, Belarus, Khazakstan (EAC); Ukraine (UA); Singapore (PSB); China (CCC); Argentina (IRAM); India (BIS); Mexico (NYCE)
Storage temperature range	-13 to 131°F
Storage temperature range	-25 to 55°C
Supported Primary Applications	Line drawings; Presentations; Renderings
Theoretical minimum line width	0.02 mm
Theoretical minimum line width	0.0008 in
UNSPSC code	43212104
UPC number	196548501700
Web address for additional information	http://www.hp.com/go/designjetstudio

Ink/Toner/Paper/Printer Supplies

Ink Supplies

★ : Recommended

HP Graphic Arts Inks/Printheads

HP 712 2-pack 80-ml Black DesignJet Ink Cartridges	3WW89A
HP 712 29-ml Cyan DesignJet Ink Cartridge	3ED67A
HP 712 29-ml Magenta DesignJet Ink Cartridge	3ED68A
HP 712 29-ml Yellow DesignJet Ink Cartridge	3ED69A
HP 712 3-pack 29-ml Cyan DesignJet Ink Cartridge	3ED77A
HP 712 3-pack 29-ml Magenta DesignJet Ink Cartridge	3ED78A
HP 712 3-pack 29-ml Yellow DesignJet Ink Cartridge	3ED79A
HP 712 38-ml Black DesignJet Ink Cartridge	3ED70A
HP 712 80-ml Black DesignJet Ink Cartridge	3ED71A
HP 712B 38-ml Black DesignJet Ink Cartridge	3ED28A
HP 712B 80-ml Black DesignJet Ink Cartridge	3ED29A
HP 713 DesignJet Printhead Replacement Kit	3ED58A

Accessories

Paper Handling

★ : Recommended

Spindles

HP DesignJet 24-in Spindle

B3Q36A

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 28, 2024 2:50 PM UTC+0000