

ProductSheet

HP LaserJet Pro MFP 4101fdw Printer (2Z619F)



Power office productivity with blazing speed, reliable hardware, and connectivity.

This printer is built for maximum productivity with fast speeds and reliable hardware, delivering effortless everyday use from wherever work happens so you can focus more on your business.



Maximum productivity.

Support your dynamic workteam with this high-speed smart printer, ideal for up to 10 users.

Seamless management.

Centralize print management for your enterprise. HP Web JetAdmin makes it easy with its suite of features.[4]

HP Wolf Pro Security.

Get printer security out of the box. Preconfigured settings mean it's ready when you are.

Featuring

Large workteam solution.

HP Pro-class print speed [1]

Dual-sided scanning.

Simple shortcuts.

Walk-up USB

HP Smart. [2]

Specifications

| | |
|---|---|
| Print Resolution Technologies | HP FastRes 1200, HP ProRes1200, Economode |
| Print quality black (best) | FineLines (1200 x 1200 dpi) |
| Print speed black (ISO, A4) | Up to 40 ppm |
| Print speed black (ISO, letter) | Up to 42 ppm |
| Print speed | Prints up to 42/40 ppm (LTR/A4) |
| Functions | Print, copy, scan, fax |
| Duplex printing | Automatic (default) |
| Duty cycle (monthly, A4) | Up to 80,000 pages |
| Duty cycle (monthly, letter) | Up to 80,000 pages |
| Printer smart software features | Auto duplex and booklet printing, N-up printing, collation, watermarks, install printer driver only, Economode for toner savings, accepts a variety of paper sizes and types ^[1] |
| Scanner advanced features | Copy preview |
| Fax smart software features | Auto fax reduction; Auto redialing; Delayed sending; Fax forwarding; TAM interface; Junk barrier; Distinctive ring detection; Cover page; Block fax; Billing codes; Save and load; Fax activity reports; Dial prefix setting; Print fax log; HP Digital Fax |
| Energy savings feature technology | HP Auto-On/Auto-Off Technology; Instant-on Technology; EcoSmart black toner |
| Replacement cartridges | HP 148A Black Original LaserJet Toner Cartridge (~2,900 pages), W1480A; HP 148X Black Original LaserJet Toner Cartridge (~9,500 pages), W1480X ^[4] |
| Supplies feature | HP JetIntelligence Cartridge |
| Connectivity, standard | 1 Hi-Speed USB 2.0; 1 rear host USB; 1 Front USB port; Gigabit Ethernet 10/100/1000BASE-T network; 802.3az(EEE); 802.11b/g/n/2.4/5 GHZ Wi-Fi radio + BLE |
| Modem | 33.6 kbps |
| Network capabilities | Yes, via built-in 10/100/1000Base-TX Ethernet, Gigabit; Auto-crossover Ethernet; Authentication via 802.1X |
| Mobile printing capability | HP Smart App; Apple AirPrint™; Mopria™ Certified; Wi-Fi® Direct Printing; Optional ROAM Queue Printing; HP ROAM For Business |
| Network protocols, supported | TCP/IP, IPv4, IPv6; Print: TCP-IP port 9100 Direct Mode, LPD (raw queue support only), Apple AirPrint™, Mopria, IPP Print; Discovery: SLP, Bonjour, Web Services Discovery; IP Config: IPv4 (BootP, DHCP, AutoIP, Manual), IPv6 (Stateless Link-Local and via Router, Statefull via DHCPv6), SSL Security and Certificate management; Management: SNMPv1, SNMPv2, SNMPv3, HTTP/HTTPS, Syslog, FTP FW Download |
| Software included | No software solutions are included in the Box only on http://hp.com ; http://123.hp.com ; |
| Compatible Operating Systems | Windows 11; Windows 10; Windows 7; Windows Client OS; Android; iOS; Mobile OS; macOS 10.15 Catalina; macOS 11 Big Sur; macOS 12 Monterey; Chrome OS |
| Technical features | AirPrint; Automatic two-sided printing; Compact size; ENERGY STAR®; Ethernet; Fast First Page Out; HP Auto-On/Auto-Off; JetIntelligence Toners; Private Print via PIN; Professional print quality; Touchscreen; Scan-to-cloud; Scan-to-email; Scan-to-folder; Wireless Direct; Wireless; Walk-up USB (doc, ppt, pdf, jpg); ADF |
| Sustainable impact specifications | Recyclable through HP Planet Partners; Compatible with Accessibility Accessories; Contains post-consumer recycled plastic |
| Energy star certified | Yes |
| Ecolabels | ENERGY STAR® qualified; EPEAT® Silver; IT ECO Declaration |
| Blue Angel compliant | No, please refer to the ECI (Ecolabel Comparison Information) document |
| Copy speed (black, normal quality, A4) | Up to 40 cpm |
| Copy speed black (normal, letter) | Up to 42 cpm |
| Copy speed black duplex (A4) | Up to 34 cpm |
| Copy speed black duplex (Letter) | Up to 36 cpm |
| Fax Resolution Black (best) | Up to 300 x 300 dpi |
| Faxing | Yes |
| Scan speed (normal, A4) | Up to 29 ppm/46 ipm (b&w), up to 20 ppm/34 ipm (color) |
| Scan speed (normal, letter) | Up to 31 ppm/49 ipm (b&w), up to 21 ppm/36 ipm (color) |
| Scan file format | PDF, JPG, TIFF |
| Scan input modes | Front-panel scan, copy, email, or file buttons; HP Scan software; and user application via TWAIN or WIA |
| Scan technology | Contact Image Sensor (CIS) |

| | |
|---------------------------------------|--|
| Scanner type | Flatbed, ADF |
| Display area (imperial) | 2.13 x 1.59 in |
| Display area (metric) | 5.4 x 4.05 cm |
| Display | 2.7" (6.86 cm) intuitive color touchscreen (CGD) |
| Minimum dimensions (W x D x H) | 420 x 390 x 323 mm (without trays and covers not extended) |
| Minimum dimensions (W x D x H) | 16.54 x 15.35 x 12.72 in (without trays and covers not extended) |
| Weight | 12.6 kg |
| Weight | 27.78 lb |
| Power consumption | 510 watts (active printing), 7.5 watts (ready), 0.9 watts (sleep), 0.9 watts (Auto Off/Wake on LAN, enabled at shipment), 0.06 watts (Auto-off/Manual-on), 0.06 (Manual Off) (Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.) |
| Power supply type | Internal (Built-in) power supply |
| What's in the box | HP Black Original LaserJet Toner Cartridge; Getting Started Guide; Support Flyer; Warranty Guide; Regulatory Flyer; Power cord ^[2] |
| Manufacturer Warranty | One-year Bench/Depot Repair warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 4E; wty ID A033) |

Top Recommended Displays, Accessories and Services

Imaging and Printing Commercial Care Pack Services

| | |
|--|--------|
| HP 3 year Next Business Day Advanced Exchange Service for LaserJet Pro MFP 410x | U42U6E |
| HP Installation Service with network configuration for Personal Scanner and Printer (1 unit) | U9JT1E |

Imaging and Printing Hardware Support Onsite Svc

| | |
|---|--------|
| HP 3 year Next Business Day Service for LaserJet Pro MFP 410x | U42TZE |
|---|--------|

Messaging Footnotes

[1] Measured using ISO/IEC 24734 and excludes first set of test documents. For more information, see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity.

[2] Requires the HP Smart app download. For details on local printing requirements see www.hp.com/go/mobileprinting. Certain features/software are available in English language only, and differ between desktop and mobile applications. Subscription may be required; subscription may not be available in all countries. See details at www.hpsmart.com. Internet access required and must be purchased separately. HP account required for full functionality. List of supported operating systems available in app stores. Fax capabilities are for sending a fax only. After 2 years, monthly fee applies to continue advanced features with HP Smart Advance. HP Smart Advance is not available in all countries. For more information, see www.hpsmart.com.

[4] HP Web Jetadmin is available for download at no additional charge at hp.com/go/webjetadmin.

Technical Specifications Footnotes

[1] Job Storage feature requires a purchase of separate USB flash drive with a minimum of 16 GB capacity.

[2] For yield information on the cartridge included with your printer, see <http://www.hp.com/go/toneryield>. Yield values measured in accordance with ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors.

[4] Declared yields based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see <http://www.hp.com/go/toneryield>

Learn more at
hp.com

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

