

P400 MINI SHORT THROW PROJECTOR

BIGGER SCREEN FROM A SHORTER DISTANCE



NATIVE FULL HD
1080P RESOLUTION



2-HOUR
BATTERY



0.7:1 SHORT
THROW RATIO



100" SCREEN
AT JUST 5 FEET
DISTANCE

1080p
FULL HD



GENERAL SPECIFICATIONS

Audio Output: 2W Hi-Lo Frequency
Stereo Speakers/ Headphone Mini-Jack
Color: Black/ Gray
Battery Size: 38 Watts (10,000 mah)
File Playback: USB Stick (up to 64GB),
Micro SD/ TF Card (up to 64GB)
Menu Language: English, Spanish, French, German, Italian, Chinese
Aspect Ratio Control: 16:9
Dimension: 4.5 in x 4 in x 2.3 in
Weight: 19.8 oz
Supported Formats: MP3 / WMA / OGG / WAV / AVI / JPG / GIF
Conformance: CE, FCC Class A



INPUTS & OUTPUTS

Audio Out: 2W Speaker, 3.5mm Stereo Headphone Jack
USB: Full-Sized USB 2.0
SD Card: Micro SD / TF Card
Video in: Digital AV, 1080P (1920x1080)
USB Power Output: 5V 1A



PROJECTION SYSTEM

Brightness : 400 LED Lumens
Projection Image: 16 - 180 inches
Projection Lens: Manual Focus
Throw Ratio: 0.7:1
Operating System: Linux
Light Source Life: 30,000 Hours LED
Native Resolution: 1080P (1920x1080)
Battery Life (Eco Mode): 2 Hours

SPECIAL FEATURES



NATIVE 1080P
FULL HD RESOLUTION



0.7:1 THROW RATIO
(SHORT THROW)



2- HOUR BATTERY (ECO MODE)
TRULY PORTABLE



SMALL & LIGHTWEIGHT
4.5" X 4" X 2.3"