

Xerox® VersaLink® Colour Printers

Unrivalled Colour, Reliability and Performance.



C8000 AND C9000

ConnectKey®
Technology

xerox™

Xerox® VersaLink® C8000 and C9000 Colour Printers

When you need professional colour, flawless reliability and top productivity in a well-connected printer, count on the VersaLink® C8000 and C9000 Colour Printers with Xerox® ConnectKey® Technology. The feature-rich, app-enabled C8000 is ready to be customized as your workplace assistant. The C9000 adds greater media flexibility and precision colour matching and control tools for graphic arts professionals and creative agencies.

VIBRANT COLOR. BIG PERFORMANCE. TOP RELIABILITY.

Right out of the box, you'll count on the Xerox® VersaLink® C8000 and C9000 Colour Printers to consistently and flawlessly perform the tasks that make your business work more efficiently. From IT-free installation wizards to step-by-step configuration options, you're ready to go — hassle free.

Designed for superior reliability, the VersaLink® C8000 and C9000 Colour Printers feature a new hardware design with fewer moving parts, strengthened paper path components and an advanced imaging system.

VersaLink® devices are loaded with features designed to reduce inefficiency. Device management and user training can be done anywhere with the time-saving Remote Control Panel.

Count on superior print quality to make your work look its best. A print resolution of up to 1200 x 2400 dpi delivers sharp text and fine line detail, plus exceptional colour vibrancy that enhances business communications — even on oversize media.

INTUITIVE. POWERFUL. READY FOR ANY JOB.

Users on the go get more done in less time with native @printbyXerox support. They simply submit their print job from any email-enabled device. Once at work, they securely login to @printbyXerox on the VersaLink® C8000 or C9000 to retrieve their job. And with Simple ID, individual users and groups enter a user ID and password once and then enjoy fast, secure access to task-specific presets, individualized favourite contacts and

commonly used apps on a personalized home screen.

Whether your documents are colour or black and white, letter-size or oversize, the VersaLink® C8000 and C9000 Colour Printers have the power and features you need to handle even the most challenging print jobs.

CONNECT TO WHAT YOU WANT, WHEN YOU WANT.

Easily add connectivity to Google Drive™, Microsoft® OneDrive® and Dropbox™ and access additional options through the Xerox App Gallery.

VersaLink® devices deliver for today's mobile worker with Apple® AirPrint®, Google Cloud Print™, Xerox® Print Services plug-in for Android™, Near Field Communication (NFC) Tap-to-Pair and Mopria®, plus optional Wi-Fi® and Wi-Fi Direct®.

Learn more about why Xerox is the only choice for today's mobile professionals by visiting www.xerox.ca/en-ca/office/mobile-solutions.

ENVIRONMENTAL STEWARDSHIP.

VersaLink® devices meet or exceed the requirements of the world's most widely recognized certifications for product environmental performance, including EPEAT®, which verifies manufacturer claims regarding design, production, energy use and recycling. **(See the complete list of EPEAT-verified VersaLink® products.)**

For more information about our environmental, health, safety and sustainability efforts, visit www.xerox.ca.

XEROX® CONNECTKEY® TECHNOLOGY

Intuitive User Experience

A familiar way to interact that includes a tablet-like experience with gesture-based touchscreen controls and easy customization.

Mobile and Cloud Ready

Instant connectivity to cloud and mobile devices right from the user interface, with access to cloud-hosted services that let you work where, when and how you want.

Benchmark Security

Comprehensive security that includes a powerful mix of built-in features and services to prevent unauthorized access, detect suspect or malicious behaviour, and protect data and documents.

Enables Next Generation Services

Easy integration of Xerox® Intelligent Workplace Services. Enables remote monitoring of service delivery and consumables.

Gateway to New Possibilities

Instantly extend your capabilities with real-world apps from the Xerox App Gallery, or talk with one of our partners to design and develop a solution specific to your business needs.

Find out more about how you'll work smarter at www.xerox.ca/en-ca/connectkey.



Xerox® VersaLink® C8000 Colour Printer

Print. Mobile connectivity.

- 1 Card Reader Bay** and internal card reader compartment.
- 2 Front-Side USB Port¹** allows users to quickly print from any standard USB memory device.
- 3 100-Sheet Bypass Tray** handles media sizes from 3.5 x 3.9 in. to 12.6 x 19 in./88.9 x 98.4 mm to 320 x 482.6 mm and banners from 12.6 x 52 in./320 x 1,320.8 mm (64 to 350 gsm).
- 4 Tray 1** handles up to 520 sheets with custom sizes of 3.9 x 5.8 in. to 11.7 x 17 in./100 x 148 mm to 297 x 431.8 mm (64 to 300 gsm).
- 5 Tray 2** handles up to 520 sheets with custom sizes of 3.9 x 5.8 in. to 12.6 x 18 in./100 x 148 mm to 320 x 457.2 mm (64 to 300 gsm).

MULTIPLE PAPER TRAY OPTIONS TO FIT EVERY NEED.

- 6 Optional Envelope Kit** (replaces Tray 1) provides trouble-free feeding of up to 50 envelopes.
- 7 Tandem Tray Module** adds up to 2,000 sheets; 8.5 x 11 in./A4, B5 (64 to 300 gsm).
- 8 Two Tray Module** adds up to 1,040 sheets with custom sizes of 3.9 x 5.8 in. to 12.6 x 18 in./100 x 148 mm to 320 x 457.2 mm (64 to 300 gsm).
- 9 High Capacity Feeder** adds up to 2,000 sheets with standard sizes of 8.5 x 11 in., 7.25 x 10.5 in./A4, B5 (64 to 216 gsm).



Xerox® VersaLink® C9000 Colour Printer

Print. Mobile connectivity.

ADD INCREASED VERSATILITY WITH FINISHING OPTIONS.

- 10 Dual Offset Catch Tray** (standard when finishers are not attached): 250 sheets each tray.
- 11 Optional Office Finisher** gives you advanced finishing functions at a great value and offers optional crease/score and saddle-stitch booklet making capable of 60-page booklets (2 to 15 sheets).
- 12 Optional BR Booklet Maker Finisher** provides the capability to create 64-page saddle-stitched booklets (2 to 16 sheets).

¹ USB port can be disabled.

INTRODUCING TOUCHSCREEN SUPERIORITY

Meet our all-new, 5-inch colour touchscreen — the user interface that sets a higher standard for customization, personalization and versatility.

By presenting a familiar “mobile” experience — with support for gestural input and task-focused apps that share a common look and feel — fewer steps are needed to complete even the most complex jobs.

A highly intuitive layout guides you through every task from start to finish, with a natural hierarchy placing critical functions near the top of the screen and commonly used options front and center. Don't like where a function or app is located? Customize the layout to make it yours.

This unmatched balance of hardware technology and software capability helps everyone who interacts with the VersaLink® C8000 and C9000 Colour Printers get more work done, faster.



Xerox® VersaLink® C8000 and C9000
Default Configuration



Xerox® VersaLink® C8000 and C9000



The VersaLink® C8000 and C9000 Colour Printers are built on Xerox® ConnectKey® Technology.

For more information, visit www.xerox.ca/en-ca/connectkey.

DEVICE SPECIFICATIONS		VersaLink® C8000	VersaLink® C9000
Speed ¹		Up to 45 ppm letter/A4	Up to 55 ppm letter/A4
Monthly Duty Cycle ²		205,000	270,000
Hard Drive/Processor/Memory		1.6GHz ARM Dual-Core/4 GB/Optional 320GB HDD	
Connectivity		Ethernet 10/100/1000Base-T, High-speed USB 3.0, Wi-Fi® and Wi-Fi Direct® with optional Wi-Fi Kit, NFC Tap-to-Pair	
Controller Features		Configuration Cloning, Xerox Extensible Interface Platform®, Xerox® App Gallery App, Xerox® Standard Accounting Tool, Role-Based Permissions, Convenience Authentication Enabled	
Print Resolution		Up to 1200 x 2400 dpi	
First-print-out Time		As fast as 11 seconds colour/11 seconds black and white	As fast as 10.5 seconds colour/10 seconds black and white
Page Description Languages		PCL® 5c/PCL 6/PDF/XPS/TIFF/JPEG/HP-GL®/Adobe® PostScript® 3™	
Colour Management		Embedded spot colour table, Xerox Colour Corrections	Embedded spot colour table with the ability to swap out PANTONE® approved colour table, Custom spot colour editor, optional Xerox® Precise Colour Management System software
Paper Input	Standard	Bypass Tray: Up to 100 sheets; Custom sizes: 3.5 x 3.9 in. to 12.6 x 19 in./88.9 x 98.4 mm to 320 x 482.6 mm; Banners: 12.6 x 52 in./320 x 1,320.8 mm (C8000: 64 to 300 gsm; C9000: 64 to 350 gsm) Tray 1: Up to 520 sheets; Custom sizes: 3.9 x 5.8 in. to 11.7 x 17 in./100 x 148 mm to 297 x 431.8 mm (64 to 300 gsm) Tray 2: Up to 520 sheets; Custom sizes: 3.9 x 5.8 in. to 12.6 x 18 in./100 x 148 mm to 320 x 457.2 mm (64 to 300 gsm)	
	Optional	Two Tray Module: Up to 1,040 sheets; Custom sizes: 3.9 x 5.8 in. to 12.6 x 18 in./100 x 148 mm to 320 x 457.2 mm (64 to 300 gsm) Tandem Tray Module: Up to 2,000 sheets; 8.5 x 11 in., 7.25 x 10.5 in./A4, B5 (64 to 300 gsm) High Capacity Feeder: Up to 2,000 sheets; 8.5 x 11 in., 7.25 x 10.5 in./A4, B5 (64 to 216 gsm) Envelope Tray (replaces Tray 1): Up to 50 envelopes: #10 Commercial, Monarch, DL, C4, C5, C6 (75 to 90 gsm)	
Paper Output/Finishing	Standard	Dual Offset Catch Tray (standard when finishers are not attached): 250 sheets each	
	Optional	Office Finisher: 2,000-sheet stacker, 50 sheets stapled, 3-position stapling, optional hole punch, optional booklet maker (score, saddle stitch) BR Booklet Maker Finisher: 1,500-sheet stacker and 500-sheet top tray, 50-sheet multiposition stapling and 2/3-hole punching plus saddle-stitch booklet making (2 to 16 sheets, 64 pages) and V-folding	
Automatic Two-sided Printing		Standard	
INTUITIVE USER EXPERIENCE			
Customize and Personalize		Walkup customization, Personalize Home Screen by User, Multiple Home Screens with Simple ID, Customize by Site, Function or Workflow with Xerox App Gallery and Xerox® App Studio	
Print Drivers		Job Identification, Bi-directional Status, Job Monitoring and Xerox® Global Print Driver®	
Xerox® Embedded Web Server		PC or mobile—Status Information, Responsive Design, Settings, Device Management, Cloning	
Remote Console		Remote Control Panel	
Print Features		Print from USB, Secure Print, Sample Set, Personal Print, Saved Job, Earth Smart Driver Settings, Job Identification, Booklet Creation, Store and Recall Driver Settings, Bi-directional Real-time Status, Scaling, Job Monitoring, Application Defaults, Two-sided Printing (DN configuration), Skip Blank Pages, Draft Mode	
MOBILE AND CLOUD READY			
Mobile Printing		Apple® AirPrint® ³ , Google Cloud Print™ Ready, Xerox® Print Services plug-ins for Android™, Mopria® Print Service Plug-ins for Android™, Xerox® @printbyXerox App	
Mobility Options		Xerox® Mobile Print and Mobile Print Cloud, Connect via NFC/Wi-Fi Direct Printing. Visit www.xerox.ca/en-ca/office/mobile-solutions for available apps.	
Cloud Connectors ⁴		Print from Google Drive™, Microsoft® OneDrive®, Dropbox™, Microsoft Office 365®, Box®, Xerox® DocuShare® Platform and more	
BENCHMARK SECURITY			
Network Security		IPsec, HTTPS, Network Authentication, SNMPv3, SSL/TLS, Security Certificates, Pre-installed Self-signed Certificates	
Device Access		Firmware Verification, User access and internal firewall, Port/IP/Domain Filtering, Audit Log, Access Controls, User Permissions, Smart Card-Enabled (CAC/PIV/.NET), Xerox® Integrated RFID Card Reader, Trusted Platform Module (TPM)	
Data Protection		Setup/Security Wizards, Job Level Encryption via HTTPS/IPPS submission, Encrypted hard disk (AES 256-bit, FIPS 140-2) and image overwrite ⁵ , Encrypted Apps with Embedded Certificate Support	
Document Security		Secure Print	
ENABLES NEXT GENERATION SERVICES			
Print Management		Xerox® Standard Accounting; Optional: Xerox® Workplace Cloud/Suite, Nuance Equitrac, Ysoft SafeQ, PaperCut and more at www.xerox.ca/en-ca/office/software-solutions#printmanagement .	
Managing Print		Xerox® Device Manager, Xerox® Support Assistant App, Auto Meter Read, Managed Print Services tools	
Sustainability		Cisco EnergyWise®, Earth Smart Printing, EPEAT-verified, Print User ID on margins	
GATEWAY TO NEW POSSIBILITIES			
Xerox App Gallery		Many apps and cloud services available. Visit www.xerox.com/appgallery for a growing selection of Xerox® Apps available for adding functions.	

¹ Declared print speed in accordance with ISO/IEC 24734. ² Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; ³ Visit www.apple.com for AirPrint Certification list ⁴ Optional download from Xerox App Gallery to the Printer — www.support.xerox.com/en-ca/product/xerox-app-gallery/documentation; ⁵ HDD required for image overwrite.

Certifications

To view the latest list of certifications, go to www.xerox.com/OfficeCertifications.

Supplies

Standard Capacity Toner Cartridges for C8000:

Black: 12,600 pages ⁶	106R04037
Cyan: 7,600 pages ⁶	106R04034
Magenta: 7,600 pages ⁶	106R04035
Yellow: 7,600 pages ⁶	106R04036
High Capacity Toner Cartridges for C8000:	
Black: 20,900 pages ⁶	106R04049
Cyan: 16,500 pages ⁶	106R04046
Magenta: 16,500 pages ⁶	106R04047
Yellow: 16,500 pages ⁶	106R04048

Standard Capacity Toner Cartridges for C9000:

Black: 18,900 pages ⁶	106R04065
Cyan: 12,300 pages ⁶	106R04062
Magenta: 12,300 pages ⁶	106R04063
Yellow: 12,300 pages ⁶	106R04064
High Capacity Toner Cartridges for C9000:	
Black: 31,400 pages ⁶	106R04077
Cyan: 26,500 pages ⁶	106R04074
Magenta: 26,500 pages ⁶	106R04075
Yellow: 26,500 pages ⁶	106R04076
Routine Maintenance Items:	
Drum Cartridge: 190,000 pages each colour ⁷ / 190,000 pages black ⁷	101R00602
Waste Cartridge: Up to 47,000 pages ⁷	108R01504
IBT Cleaner: Up to 160,000 pages ⁷	104R00256
Transfer Roller: Up to 200,000 pages ⁷	116R00015

Options

Xerox® Precise Colour Management System software for C9000DT	097S04974
Two Tray Module	097S04969
Tandem Tray Module	097S04970
High Capacity Feeder	097S04845
Envelope Tray (Replaces Tray 1)	497K17880
Office Finisher	097S05019
2/3 Hole Punch for Office Finisher	497K20600
Booklet Maker for Office Finisher	497K20590
Booklet Maker Finisher with 2/3 Hole Punch (comes with Horizontal Transport)	497K21000
HDD (320 GB Hard Drive for C8000)	097S04971
Wireless Network Adapter (Wi-Fi Kit)	497K16750
Internal Card Reader/RFID Kit	497K18120

⁶ Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

⁷ Approximate pages. Declared yield will vary depending on job run length, media size/orientation and machine speed.

For more information, visit <http://www.office.xerox.com/latest/SUPGL-01.PDF>. Configurations vary by geographical location.

For more detailed specifications, go to www.xerox.ca/office/latest/VC8SS-01C.pdf or www.xerox.ca/office/latest/VC9SS-01C.pdf.

© 2021 Xerox Corporation. All rights reserved. Xerox®, ConnectKey®, DocuShare®, Global Print Driver®, VersaLink®, and Xerox Extensible Interface Platform® are trademarks of Xerox Corporation in the United States and/or other countries. The information in this brochure is subject to change without notice. 03/21 TSK-1693 BR26549 VC8BR-01CF

