

## ASUS Mini PC PN series Easy Modification Maximum possibilities

### Upgrade-friendly

It harnesses the power of the latest 11th Generation Intel® Core™ processor combined Intel® Iris® Xe\*. There's also an ultrafast PCIe® Gen4 SSD to ensure fast boot times and rapid app loads.

\*Only available with Intel® Core™ i5 & i7 SKUs


\*Intel® Iris® Xe Graphics requires 128-bit dual channel memory for optimal performance

### Triple storage

An optional multi-storage design that accommodates up to two M.2 SSD and a 2.5-inch solid-state drives(SSD) or hard disk drives (HDD) for added storage flexibility.

### Extreme cooling

Our self-cleaning fan module keeps the CPU operating at optimum temperatures and enables stronger performance that lasts. Anti-Dust Self-Cleaning System not only keeps the heatsinks clean, but also effectively ejects the dust and other particle to prolong the lifespan of the system.



### Accessories list:



<b>Model</b>		<b>PN63-S1</b>
<b>OS</b>		Windows®11 64Bit, Windows®11 Pro 64Bit, Windows®10 Pro 64Bit or W/O OS
<b>CPU</b>		Intel® Core™ i7-11370H, i5-11300H (cTDP 35W) Intel® Core™ i7-1165G7, i5-1135G7, i3-1115G4 (cTDP 28W)
<b>Chipset</b>		Integrated
<b>Graphics</b>		Integrated - Intel® UHD Graphics (i3) or Intel® Iris® Xe Graphics (i5/i7) *Intel® Iris® Xe Graphics requires 128-bit dual channel memory for optimal performance
<b>Memory</b>		Memory support 2 x SO-DIMM DDR4 3200 MHz (4GB, 8GB, 16GB or 32GB)
<b>Storage</b>		Storage support 1 x 2.5" SATA HDD, 2 x M.2 PCIe NVMe SSD (128G, 256G, 512G or 1TB)
<b>Wireless Network</b>		Intel® Wi-Fi 6 AX200 (Gig+) and BT V5.2, 2*2 Intel® Wi-Fi 6 AX201 (Gig+) and BT V5.2, 2*2 Mediatek Wi-Fi 6 MTK7921 and BT V5.2, 2*2 Intel® 9560 802.11ac and BT V5.1, 2*2  *Bluetooth version support may vary from OS. Bluetooth v5.2 function will be ready in Windows 11 or later.
<b>LAN</b>		Intel® LAN, 10/100/1000/2500 Mbps Onboard: Intel® I225V Configurable port: Intel® I225V Supports Wake on LAN / PXE / Auto Power on / RTC Wake
<b>Interface</b>	<b>Front I/O</b>	1 x USB 3.2 Gen2 Type-C 1 x USB 3.2 Gen2 1 x Audio Jack (Line out/ Mic in/ Headphone out)
	<b>Side I/O</b>	1 x Kensington Lock 1 x 3-in-1 carder (Micro SD/Micro SDHC/Micro SDXC)
	<b>Rear I/O</b>	2 x USB 3.2 Gen2 1 x Mini Display 1.2 Port 1 x HDMI 1.4 Port 1 x Configurable Port (options: Display Port 1.4/ COM/ VGA) 1 x Intel (RJ45) 2.5G LAN 1 x DC-in 1 x Padlock ring *Supports up to 3 display simultaneously
<b>TPM</b>		fTPM 2.0 or TPM 2.0 chip (Optional)
<b>BIOS Function</b>		64 Mb Flash ROM, UEFI AMI BIOS, PnP, DMI2.0, WfM2.0, SM BIOS 2.8, ACPI 5.0, Multi-language BIOS, ASUS EZ Flash 3, ASUS CrashFree BIOS 3, My Favorites, Quick Note and ASUS DRAM SPD (Serial Presence Detect) memory information
<b>Software</b>		ASUS Business manager, MyASUS, ASUS Product registration program, Asus Control Center test, Watchdog timer
<b>Power Supply</b>		19.5Vdc, 4.62A 90.0W Power Adapter (80cm)
<b>Physical</b>	<b>Dimension</b>	120 x 130 x 58 mm (0.9L)
	<b>Weight</b>	0.9 kg (Including 2.5" HDD)
<b>Max Resolution</b>	<b>HDMI</b>	4096x2160 @ 60 Hz
	<b>DP</b>	5120x2160 @ 60 Hz
	<b>VGA</b>	1920x1200 @ 60 Hz
<b>Temperature</b>	<b>Operating</b>	0°C~50°C
	<b>Storage</b>	-40°C~85°C
<b>Humidity</b>		0%~95% Relative Humidity
<b>Acoustic</b>	<b>Idle mode</b>	<29 dBA
	<b>Full loading</b>	<38 dBA  * Test results will vary slightly depending on the HDD/SSD SKU selected by customer
<b>Certificates</b>		BSMI / CB / CE / FCC / UL / CCC / Energy Star / C-Tick / WiFi / RF / VCCI