



SPECIFICATIONS

Panel Size	27" (69cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	170Hz
Response time	1ms (MPRT)
Panel Type	IPS
Brightness (nits)	250
Viewing Angle	178° (H) / 178° (V)
Aspect Ratio	16:9
Curvature	Flat
Contrast Ratio	1100:1
Active Display Area (mm)	597.888(H)x336.312(V)
Pixel Pitch (H x V)	0.3114(H)x0.3114(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Adobe RGB / DCI-P3 / sRGB	85.67% / 81.1% / 101.91%
Video ports	2x HDMI (Supports FHD@144Hz as specified in HDMI 1.4b) 1x DP (Supports FHD@170Hz as specified in DisplayPort 1.2a with overclocking)
USB ports	N/A
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Control	5-way OSD navigation joystick
Power Type	External Adaptor 20V 2.25A
Power Input	100~240V, 50/60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
ACTIVATED RANGE	48 to 170Hz
DCR	100000000:1
Color Bit	8 Bits
HDR Support	N/A
Power consumption	On-mode: 17 (KWh/1000h) / Off-mode: 0.3 (KWh/1000h)
Signal Frequency	30~100 KHz(H) / 48~170 Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	N/A
Adjustment (Pivot)	N/A

FEATURES



IPS

Wider viewing angles and the most realistic and accurate colors.



eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



170Hz High Refresh Rate

Experience smooth gaming with 170Hz refresh rate, that gives you the upperhand in fast moving games.



Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



Console Mode - FHD only

Best solution for console users: FHD@120Hz

Adjustment (Height)	N/A
Dimension (W x D x H)	612.5 x 228.2 x 454 mm 612.5 x 45 x 368.3 mm (Without stand)
Carton Dimension (W X H X D)	WW carton: 683 x 157 x 463 mm / Outer carton: 698 x 172 x 488 mm
Weight (NW / GW)	4.1kg / 5.8kg without Stand: 3.3kg
Frameless Design	Yes
Console Mode	Support FHD@120Hz
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
PIP / PBP Function	N/A
Note	Display Port: 1920 x 1080 (Up to 170Hz) HDMI: 1920 x 1080 (Up to 144Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 5-way joystick navigator
2. DC jack
3. 2 x HDMI (1.4b)
4. 1 x Display Port (1.2a)
5. Headphone out
6. Kensington lock