



## SPECIFICATIONS

<b>PANEL SIZE</b>	27"
<b>PANEL RESOLUTION</b>	1920 x 1080 (FHD)
<b>REFRESH RATE</b>	75Hz
<b>RESPONSE TIME</b>	5ms
<b>PANEL TYPE</b>	IPS
<b>VIEWING ANGLE</b>	178°(H) / 178°(V)
<b>ASPECT RATIO</b>	16:9
<b>CONTRAST RATIO</b>	1000:1 (TYP)
<b>sRGB</b>	100% (CIE 1976)
<b>ACTIVE DISPLAY AREA (MM)</b>	597.888(H) x 336.312(V)
<b>PIXEL PITCH (H X V)</b>	0.3114(H) x 0.3114(V)
<b>SURFACE TREATMENT</b>	Anti-glare
<b>DISPLAY COLORS</b>	16.7M
<b>COLOR BIT</b>	8 bits
<b>VIDEO PORTS</b>	1x HDMI™ (2.0b), 1x DisplayPort (1.2a), 1x Type C (DP Alternate) with 65W power delivery
<b>USB Ports</b>	1x USB 2.0 Type B, 2x USB 2.0 Type A
<b>AUDIO PORTS</b>	1x Headphone-out
<b>KENSINGTON LOCK</b>	Yes
<b>SPEAKER</b>	2x 2W
<b>VESA MOUNTING</b>	75 x 75 mm
<b>POWER TYPE</b>	External Adaptor (19V 5.79A)
<b>POWER INPUT</b>	100~240V, 50~60Hz
<b>ADJUSTMENT (TILT)</b>	-5° ~ 20°
<b>ADJUSTMENT (SWIVEL)</b>	-30° ~ 30°
<b>ADJUSTMENT (PIVOT)</b>	-90° ~ 90°
<b>ADJUSTMENT (HEIGHT)</b>	0 ~ 110mm
<b>DIMENSION (W X H X D)</b>	613.5 x 401.5 x 200.81 mm (24.15 x 15.81 x 7.91 inch)
<b>WEIGHT (NW / GW)</b>	5.85 kg (12.90 lbs) / 8.1 kg (17.86 lbs)
<b>CERTIFICATES</b>	CB/CE
<b>VIDEO INPUT COMPATIBILITY</b>	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
<b>Note</b>	HDMI™: 1920 x 1080 (Up to 75Hz) DisplayPort: 1920 x 1080 (Up to 75Hz) Type-C: 1920 x 1080 (Up to 75Hz)

## FEATURES



### IPS Grade Panel

Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video



### EyesErgo

An eye care solution designed with ergonomics in mind.



### Less Blue Light PRO

Use a hardware solution to reduce the light emission in the blue-violet region of the blue light spectrum (wavelength 415 to 455 nm).



### Anti-Flicker technology

MSI Anti-Flicker technology provides a very comfortable viewing experience by reducing the amount of screen flicker.



### Productivity Intelligence App (P.I.)

The Productivity Intelligence App (P.I.) provides the smartest tool, KVM function, color & display mode to you while working with it every day




### KVM Function Support

Control multiple devices via one set of keyboard, mouse, and MSI monitor.



### Type C 65W Power Delivery

Built-in an USB Type-C connection with 65W power delivery allows you to effortlessly connect to and charge your devices



### Adjustable Stand

Adjust the stand to the angle that is most suitable for you to keep yourself work comfortably.



### Built-In Speaker

Built-in speakers allow you to listen clearly without connecting external speakers.

## CONNECTIONS



1. 1x DC Jack
2. 1x Type C (DP Alternate)
3. 1x DisplayPort (1.2a)
4. 1x HDMI™ (2.0b)
5. 1x Headphone-out
6. 1x USB 2.0 Type B
7. 2x USB 2.0 Type A