



# 4MP Flexible Intensifier® IP Dome Camera with Advanced Analytics, NDAA

## O4FD1

2.8mm fixed lens, dark gray housing



### Features

- Flexible Intensifier® Technology to fit any lighting application
- Captures up to 4MP @ 30fps real time
- Captures color in extreme low light conditions and monochrome in absolute darkness.
- IR range: up to 98' (depending on scene reflection)
- True WDR operation
- Micro SD card slot (card not included)
- ONVIF Profile T Compliant
- IP67 Weather Resistance
- IK10 Vandal Resistance
- Built-in standard PoE (IEEE 802.3af)
- Line crossing with counting/Intrusion detection\*
- Face/People/Vehicle detection\*
- Junction box included
- 5 year warranty



### Camera Specifications

Image Sensor	Progressive scan 1/1.8" CMOS
Maximum Resolution	2560 x 1440
Field of View	Horizontal: 111.3°; Vertical: 78.9°; Diagonal: 118.4°
Minimum Illumination	0.0016 lux@F1.6, AGC ON; 0 lux with IR
White Balance	Auto, Indoor, Outdoor, Manual
Compensation	True WDR (120dB), BLC, HLC
Day/Night	Smart IR
Electronic Shutter Speed	1s ~ 1/100000s
DNR	3D DNR
Angle Adjustment	Pan: 0°~355°; Tilt: 0°~67°; Rotation: 0°~355°

### Video Specifications

Main Resolution	2560x1440, 2304x1296, 1920x1080, 1280x720, D1, CIF, 480x240 @30fps
Substream	1280x720, D1, CIF, 480x240 @30fps
Third Stream	D1, CIF, 480x240 @30fps
Compression	Main stream: H.265+ / H.265 / H.264+ / H.264 Sub stream: H.265+ / H.265 / H.264+ / H.264 / MJPEG Third stream: H.265+ / H.265 / H.264+ / H.264 / MJPEG
Bitrate Control	VBR, CBR (64Kbps ~ 8Mbps)
Multiple Streaming	3 streams
Video Settings	Region of Interest, Privacy masking, Brightness, Contrast, Hue, Saturation, Denoise, Antiflicker, Day/Night mode, Exposure, Gain, Corridor Pattern, Image flip/mirror

### Audio Specifications

Audio Compression	G.711A / G.711 U
Audio input	Built-in mic and 3.5mm input
Audio output	No

### Client Specifications

Web Browser Support	Google Chrome, Microsoft Edge, Internet Explorer, Apple Safari
PC Application	SecureGuard® VMS and SecureGuard CMS
Mobile	SecureGuard® Client, Speco Blue

### Interfaces

Ethernet	RJ45 Jack, 10/100 Mbps, PoE
Power	12VDC input jack
Audio	Built-in mic and 3.5mm input
Card slot	MicroSD, up to 256GB (not included)
Alarm	1 ch input/ 1 ch output
Reset	Yes

### Network Specifications

Protocols	UDP, IPv4, IPv6, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, SNMP, 802.1x, UPnP, HTTP, HTTPS
DDNS support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP/MAC address filtering, digest authentication, Watermark, and illegal login lock
User Access	Max. 10 simultaneous users Actual number of users may vary depending on bandwidth

### System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection, Object abandoned/missing detection, region entrance/exiting/intrusion detection (people/vehicle classification), line crossing detection (people/vehicle classification), video tampering detection, scene change detection, face detection, face capture.
Alarm Triggers	Motion detection, Sensor detection, SD card error, SD card full, IP address conflict, cable disconnection
Alarm Events	FTP upload, email upload

### Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	5.5W (max)
Operating Temperature	-40°F - 140°F
Operating Humidity	less than 95% (non-condensing)
Unit dimensions	4.68" (Φ) x 3.5" (H)
Unit Weight	1.43 lbs
Certifications	FCC

**NDAA COMPLIANT**

\*with compatible Speco Blue recorder  
\*\* Compliant with NDAA Section 889 Part B Guidelines



### Optional Accessories



### Cameras Interfaces



ONVIF is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Amazon's trademark is used under license from Amazon.com, Inc. or its affiliates. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 8/22/22

Apps available from the following:

Download on the App Store | GET IT ON Google Play | amazon appstore | ONVIF® 800-645-5516 • Fax: 631-957-9142 or 631-957-3880 • specotech.com

speco technologies®