



SPECIFICATIONS

Panel Size	34" (86.36 cm)
Panel Resolution	3440 x 1440 (UWQHD)
Refresh Rate	100Hz
Response time	1ms(MPRT)
Panel Type	VA
Brightness (nits)	250
Viewing Angle	178°(H)/178°(V)
Aspect Ratio	21:9
Curvature	1500R
Contrast Ratio	3000:1
Active Display Area (mm)	797.184 (H) x 333.72 (V)
Pixel Pitch (H x V)	0.23175(H) x 0.23175 (V)
Surface Treatment	Anti-glare
Display Colors	1.07B(8bit+FRC)
DCI-P3 / sRGB	86%/115%
Video ports	1x DP(Supports 3440 x 1440@100Hz as specified in DisplayPort 1.2a) 1x HDMI(Supports 3440 x 1440@100Hz as specified in HDMI1.4b) 1x HDMI(Supports 3440 x 1440@100Hz as specified in HDMI2.0b)
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	75 x 75 mm
Power Type	External Adaptor 19V 3.42A
Power Input	100~240V, 50~60Hz
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
DCR	100000000:1
Signal Frequency	58.56 to 148.1KHz(H) 48 to 100Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-5° ~ 5°
Adjustment (Height)	0 - 90mm
Dimension (W x H x D)	810 x 270 x 510 mm / 31.89 x 10.63 x 20.08 inch
Carton Dimension (W X H X D)	910 x 210 x 485 mm / 35.83 x 8.27 x 19.09 inch

FEATURES

Weight (NW / GW)	6.91 kg / 9.36 kg 15.24 lbs / 20.64 lbs
Frameless Design	Yes
Console Mode	2K Resolution PS5™ Optimization * All trademarks and the registered trademarks are the property of their respective owners.
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
Note	Display Port: 3440 x 1440 (Up to 100Hz) HDMI: 3440 x 1440 (Up to 100Hz) sRGB and DCI-P3 follow CIE1976 standard

CONNECTIONS



1. 1x HDMI 2.0
2. 1x HDMI 2.0
3. 1x Display Port 1.2a
4. 1x DC Jack
5. 1x Earphone out