

GCS1412TAA4

2-Port Single View DisplayPort KVM Switch w/Audio



2-Port Single View DisplayPort Secure KVM with Audio Protection Profile v4.0

Secure and manage multiple data-sensitive systems from one workstation from internal and external cybersecurity threats with the TAA-compliant IOGEAR 2-Port Single View DisplayPort Secure KVM with Audio Protection Profile v4.0. Enable authorized users secure access to up to four systems with one keyboard, mouse, a 4K @30Hz monitor.

Featuring the latest in Common Criteria and NIAP Protection Profile v4.0 security requirements set for the U.S. government for peripheral sharing switches, the secure KVM switches are built for multiple interfaces and ideal for use in high-security environments that demand rigorous cybersecurity provisions including military and defense, federal agencies, government, utilities, commercial and healthcare applications.

- NIAP-Certified PP4.0
 - Validated to Protection Profile for Peripheral Sharing Device v4.0
 - 2-Port Single View DisplayPort Secure KVM Switch
 - One USB console controls 2 secure computers on 1 display
 - Superior 4K UHD Video Resolution
 - UHD Resolution: 3840 x 2160 @30Hz
 - Port Selection via Push-Button and Remote Port Selector** for Enhanced Security
 - Keyboard restrictions - OSD & hotkey methods are not allowed
 - Isolated Channel per Port
 - Unidirectional data flow restricts data leakage between connected computers
 - Active Chassis Intrusion Detection
 - Compromising the unit's cover renders the switch inoperable
 - Tamper-Evident Seals
 - Visually detect attempts to gain access to switch's internal components
 - Tamper-Proof Hardware
 - Integrated circuits are soldered directly onto the circuit board to hinder component sabotage
 - Non-Reprogrammable Firmware
 - Prevents tampering and attempts to reprogram the switch's firmware
 - Clears Keyboard Buffer
 - Data clears automatically after transmission to switch and resets
 - Analog Speaker Support
 - Secure audio data input does not convert digital audio to analog audio
 - Multiplatform Support
 - Windows® 2000, Vista, 7, 8, 8.1, 10, 11 Linux, Mac OS X, & Sun
 - Rugged Metal Enclosure
 - Durable, Full Metal Chassis
 - Build-In, Internal Power Supply
- ** Remote Port Selector sold separately



Requirements

Package Contents

Console

- DisplayPort monitor capable of the highest resolution that you will be using on any computer in the installation
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse
- Speaker (optional)

- 1x GCS1412TAA4
- 1x Power Cord
- 1x User Guide
- 1x Warranty Card

Computers

- 1 x DisplayPort Video output connector
- A USB Type A port for keyboard and mouse
- A 3.5mm jack Audio port for speaker (Optional)

Operating Systems

- Win 7, 8, 10, 11
- Linux: Kernel2.6+, RedHat v6.0+, SuSE v8.2+
Mandriva(Mandrake) v9.0+
- Unix: AIX v4.3, FreeBSD v3.51+, Sun Solaris v9.0+
- Novell Netware v5.0+Mac OS v9+
- DOS v6.2+

Specifications

Function	GCS1412TAA4
Computer Connections	
Direct	2
Port Selection	
	2 x DisplayPort Female
Console Connectors	
Monitor	1 x DisplayPort Female
Keyboard	USB Type-A
Mouse	USB Type-A
Audio	1 x 3.5mm Mini Stereo Jack Female
CPU Connectors	
Monitor	2 x DisplayPort Female
Keyboard & Mouse	2 x USB Type-B Female
Audio	2 x 3.5 Mini Stereo Jack Female
Switches	
Port Selection	2 x Pushbuttons
Reset	1 x Semi-recessed Pushbutton
Power	1x Rocker
LEDs	
On Line	2 x Orange
Selected	2 x Orange
Power On	1 x Green
Key Lock	3 x Green
Console Video	1 x Green
Emulation	
Keyboard	USB
Mouse	USB
Video Resolution	
	Up to 3840 x 2160@30Hz (UHD)
Power	
Input Rating	100 - 240V, 50 - 60Hz; 1A
Environment	
Operation Temperature	0 - 50C
Storage Temperature	-20 - 60C
Humidity	0 - 80% RH, Non-condensing
Housing	
Case	Metal

Dimensions	GCS1412TAA4
Unit Dimensions	
Height	1.75" (4.44cm)
Length	13.25" (33.65cm)
Depth	6.25" (15.87cm)
Unit Package Dimensions	
Height	4.75" (12.06cm)
Length	16.5" (41.91cm)
Width	8.25" (20.95cm)
Master Carton	
Height	9.25" (23.49cm)
Length	17" (43.18cm)
Width	14.75" (37.46cm)
Master Carton Qty.	3
Weight	
Master Carton Wt.	16.8lbs (7.62kg)
Unit Pack Wt.	5.1lbs (2.31kg)
Unit Wt.	3.8lbs (1.72kg)