

Gamber-Johnson Rugged Lite Backlit Keyboard

Item #KYB012

Purchase this product through a [reseller](#) in your area.



Download

Weight

1 lbs / 0.45 kg

Height

10.31 in / 26.19 cm

Width

0.56 in / 1.42 cm

Depth

7.12 in / 18.08 cm

Gamber-Johnson's low-profile Rugged Lite Backlit Keyboard is thin, light-weight, has an ergonomic feel and is the perfect keyboard solution for a mobile office, whether in a vehicle or on a forklift. Combine this keyboard with Gamber-Johnson's custom quick-release keyboard mount to provide even more convenience.

Antenna Pass-Through

- None

Port Replicator

- USB 2.0 (500mA)

Features

- Integrated center Touchpad with right and left mouse button
- 76-key keyboard with 12 function keys for custom operation
- Integrated red backlighting with four levels of intensity and ON/OFF control (F12 Key)
- Low-profile ergonomic design for ease of use in a mobile environment
- Emergency Key - a configurable key that can be used to send for emergency help or assistance
- Silicone rubber keys with white lettering and a rugged ABS polycarbonate case
- Input cable: USB Type A male connector (1.5 m/59.0 inch cable)
- Supports Windows (XP or Above), Android, Linux, and Mac OS / iOS platforms
- USB- A port to attach a mouse, another peripheral, or flash drive (USB 2.0 500mA)
- Rubber feet to prevent slippage
- Keyboard is compatible with PMT custom keyboard tray ([AS7.T004.026](#))
- Available in US English, UK , German, French and Spanish. Contact us for other language options. Minimum Order Quantity 250 units on all languages other than US English.

Specifications

- Power: 5Vdc @ <500mA from data cord
- Designed and tested to MIL-STD 810G shock and vibration specifications
- Temperature range: OPERATING: -20°C to 60°C STORAGE: -40°C to 85°C
- Designed to IP54 ingress specifications
- Two million actuations per key

Certificates & Testing

- FCC, CE, UKCA, C-Tick, RoHS, REACH

Warranty

- 1 Year Limited Warranty