



Raider GE67HX 12UHS-069

Manufacturer Part #	RaiderGE6712069
OS	Windows 11 Pro
CPU	Core i9-12900HX 8+8Core
CPU Speed	1.5-5.0 GHz
Color	Dark Grey
Screen Size	15.6" OLED QHD, Wide View Angle 240Hz Thin Bezel, 100% DCI-P3
Resolution	2560x1440 (16:9)
GPU	NVIDIA® GeForce RTX™ 3080 TI Laptop GPU Up to 1640MHz Boost Clock, 175W Maximum Graphics Power with Dynamic Boost. Max. 220W CPU-GPU Power with MSI OverBoost Technology. *May vary by scenario.
Video Memory	16G GDDR6
Keyboard	SteelSeries per-Key RGB with Anti-Ghost key (84 Key)
Speaker	Sound by Dynaudio, 2x1W Speaker, 2x2W Duo Wave Woofer
Memory	32GB (16GB*2) DDR5 4800MHz
HDD Capacity	1TB NVMe SSD Gen4x4
HDD Interface	NVMe
LAN	Killer E3100G
WLAN	Killer WiFi 6E AX1675 (2x2)
Bluetooth	BT 5.2
Card Reader	SD7.0
Webcam	1080p FHD Webcam
USB	1x USB3.2 Gen 2; 2x USB3.2 Gen 1
Type-C Port	1x Thunderbolt™ 4; 1x USB 3.2 Gen 2/DP
Video Port	1x HDMI (8K @ 60Hz / 4K @ 120Hz)
Audio Port	1 Audio Combo (1/8")
AC Power Adaptor	330W
Battery Pack	4 cell (99.9Whr)
Dimension	14.09"x 10.51"x 0.92"
Weight	5.24 lbs
Manufacturer Warranty	1 year Limited warranty (Include 1 Year Global)